

Temporary Power
Temporary Industrial Lighting
Fluorescent Maintenance Worklights

HUBBELL

Features

- Inline power on/off switch for user convenience
- Tough shield outer tube virtually unbreakable
- 120V AC electronic ballast is protected inside the light fixture

Ordering Information

Description	UPC	Catalog Number
Fluorescent maintenance light, 34.5 in.	783585467344	HBLML5025



Listings

UL
CSA
ETL

Online Resources

[eCatalog](#)

Specifications

Light Type	Fluorescent
Plug Type	NEMA 5-15P
Length	34.5
Width	2.625

Performance

Electrical	
Lamp Life	14,000 hours
Light Color	4100 K
Lumen Output	3750
Rating	15A 125V
Wattage	50

Mechanical	
Cord Length	25 ft.
Cord Type	16/3 SJEOW

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

