



Z-Wave In-wall Smart Fan Control



Specifications

Power: 120VAC, 60Hz **Signal Frequency:** 908.4/916

Maximum Fan Motor Load: 2.5A

Range: Up to 150 feet from controller or closest Z-Wave device

Operating Temperature: 32-104° F (0-40° C)

Warranty: 2-year limited product warranty

Requires neutral wire. Switch must be mounted indoors

Control fan motor only, not intended for lighting control. No more than two fans


Design Features

- Remotely monitor with any mobile device* (wallplate not included)
- May be used in single pole installation or with up to four iDevices® model IDEVZ03DW Add-on switches in 3, 4, 5 or 6-way wiring configurations
- Turn ON/OFF and control speed level of the connected ceiling fan manually or via Z-Wave remote control (On/Off, High, Medium, Low)
- Can be included in multiple Groups and Scenes
- Supports Advanced Configuration; LED status, Invert switch (if unit is installed upside down)
- Screw Terminal installation; requires wiring connections for Line (Hot), Load, Neutral and Ground. Traveler wire required for multi pole installation
- Use a standard size wall plate for single gang installations
- Interchangeable Paddle switch: White & light almond paddle included in package
- LED can be enabled/disabled manually
- Inline traveler circuit protection

Z-Wave Plus Features

- Works with Z-Wave Classic and Z-Wave Plus Products
- 50% more wireless range
- 250% faster processor
- 400% more memory
- 50% more energy efficient
- Supports wireless upgrades


White/light almond paddles included




* Requires Z-Wave hub or controller, functions may vary depending on brand.




Single Location Wiring



Space-Saving Screw Terminals



Multi-Location Wiring



to future-proof your home

Installation Recommendations:

- Devices require a 1-gang U.S. wall box. 3½ in deep recommended, 2¼ in deep minimum.
- Indoor use only
- Visit <http://www.ezwave.com/hubs/> for hub compatibility
- Wallplates sold separately
- Trilingual Instruction manual – (English, French, Spanish)



IDEVZ07W PRODUCT SPECIFICATIONS

Device Configuration

Adding your device to a Z-Wave network


Once the hub is ready to add your smart dimmer, press and release the top or bottom button on the smart dimmer to add it in the network.

To remove and reset the device

Once the controller is ready to remove your device, press and release the top button on the smart dimmer to remove it from the network.

S2 + SmartStart install

The controller's app will indicate if it has discovered the device. If prompted by the controller to enter the S2 security code, refer to the QR code/security number on the side of the box, or the QR code label on the product. Enter the 5-digit code.



To return to factory defaults

Quickly press the ON button 3 times, then press the OFF button 3 times. The LED will flash ON/OFF 5 times when completed successfully.

Certifications & Compliances



Compliances, specifications and availability are subject to change without notice.



WIRING DEVICES-KELLEMS
HUBBELL INCORPORATED (DELAWARE)
SHELTON, CT 06484

Questions? Contact our U.S.-based Consumer Care at 1-800-288-6000.
www.hubbell-wiring.com

Related Products - iDevices® Z-Wave Plug-In Products




IDEVZ05DW
In-Wall
Smart Dimmer



IDEVZ05TW
In-Wall
Smart Dimmer



IDEVZ01DW
In-Wall
Smart Switch



IDEVZ01TW
In-Wall
Smart Switch



IDEVZ03DW
Add-On
Switch



IDEVZ03TW
In-Wall Smart
Fan Control



IDEVZ08W
Smart Tamper
Resistant
Receptacle

