

IEC Pin and Sleeve  
Watertight Devices  
Receptacle/Connector Replacement Interior



- Features
- Sequential contact engagement

Ordering Information

|                                                      |              |                |
|------------------------------------------------------|--------------|----------------|
| Description                                          | UPC          | Catalog Number |
| Pin and Sleeve Replacement Interior, For 4W 60A, IEC | 783585420820 | IN460DFS       |
| Device Color                                         |              |                |
| Black                                                |              |                |



Standards

UL Listed  
CSA Certified

Specifications

|                 |                       |
|-----------------|-----------------------|
| Gaskets         | Neoprene              |
| Hinge Spring    | Stainless Steel       |
| Contact Carrier | High-Impact Thermoset |
| Terminal Screws | Stainless Steel       |
| Assembly Screws | Stainless Steel       |

Performance

|                         |                                                                                      |
|-------------------------|--------------------------------------------------------------------------------------|
| Electrical              |                                                                                      |
| Current Interrupting    | Certified for current interrupting at full rated current                             |
| Dielectric Voltage      | Withstands 3,000V AC                                                                 |
| Max Working Voltage     | 600V AC RMS                                                                          |
| Mechanical              |                                                                                      |
| Impact Resistance       | In accordance with UL746C                                                            |
| Product Identification  | Ratings are a part of the external label and molded into the receptacle mount        |
| Terminal Identification | Terminals identified in accordance with North American and International conventions |
| Environmental           |                                                                                      |
| Flammability            | UL94-5VA and V-0 classification                                                      |
| Ingress Protection      | IP67 Suitability                                                                     |
| Operating Temperatures  | Max. Continuous:75°C; Min. Continuous:-40°C w/o impact                               |

Online Resources

eCatalog

