

IEC Pin and Sleeve

30A, 125/250V, 3 Pole, 4 Wire

Low Profile Receptacle

Features

- Compact Design
- Fully Interchangeable with IEC 60309 Devices
- Solid one-piece pins for reliable electrical contact
- Molded in durable and non conductive nylon

Ordering Information

| Description | UPC | Catalog Number |
|-------------------------------|--------------|----------------|
| IEC Pin and Sleeve Receptacle | 783585888002 | L430P12 |

Listings

UL Listed, File E146033
CSA Certified File LR280C
UL Classified to IEC 60309-1 IEC 60309-2

Specifications

| | |
|-----------------|-----------------------|
| Housing | PBT |
| Contact Carrier | High-Impact Thermoset |
| Terminal Screws | Stainless Steel |

Performance

Electrical
Current Interrupting Certified for current interruption at full rated current

Dielectric Voltage Withstands 3,000V AC
Max Working Voltage 250V RMS


Mechanical
Impact Resistance Per CSA C22.2 No. 182.1 / UL1682
Product Identification Ratings are a permanent part of the device housing
Terminal Identification Terminals identified in accordance with North American and IEC conventions

Environmental
Flammability HB or better
Ingress Protection IP22
Operating Temperatures Max. Continuous +75°C; Min. -40°C w/o impact

Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

HUBBELL



Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

