#### UL 1686 C1 Pin and Sleeve

200A, 600/250V AC/DC, 4 Pole, 5 Wire

## Insulgrip® Pin and Sleeve Corrosion Resistant Receptacle

# HUBBELL

#### **Features**

- · Watertight neoprene sealing glands for reliable seal
- · Pin chamber confines arcing within the interior chamber

#### **Ordering Information**

**Description**Pin and Sleeve, Watertight Insulgrip Receptacle

**UPC** 783585161839

Catalog Number M5200RS1

**Device Color** Aluminum

### **Standards**

UL Standard 1682

CSA Certified to CSA Spec. C22.2 No. 182.1 UL Listed and CSA Certified Type 4X

### **Specifications**

Housing
Gaskets & Seals

Contact Carrier
Pin Spring
Cover

**Epoxy Painted Aluminum** 

Neoprene

Thermoset Polyester
Beryllium Copper
Epoxy Painted Aluminum

#### **Performance**

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Max. Working Voltage Withstands 3,000V AC 600V AC RMS

Mechanical

Impact Resistance Per CSA C22.2, No. 182.1, UL 1682

Product Identification Identification and ratings are permanently fastened

to the device housing

Terminal Identification Terminals identified in accordance with UL 1686(1,

2, 3, Green)

**Environmental** 

Flammability (Enclosure) UL 94V-0 and CSA C22.2 No. 0.17

Moisture Resistance Type 3, 4, 4X per UL 50E and CSA 22.2, No. 94
Operating Temperatures Max. Continuous 75°C; Min. -40°C w/o impact -25°

with impact

## Online Resources

Customer Use Drawing eCatalog

Installation Instructions





