

## IEC Pin and Sleeve

30A, 3 Phase, 250V, 3 Pole, 4 Wire

## Low Profile Receptacle

### Features

- Compact Design
- Fully Interchangeable with IEC 60309 Devices
- Solid one-piece pins for reliable electrical contact
- Molded in durable and non conductive nylon

### Ordering Information

Description	UPC	Catalog Number
IEC Pin and Sleeve Receptacle	783585888026	L430P9

### Listings

UL Listed, File E146033  
CSA Certified File LR280C  
UL Classified to IEC 60309-1 IEC 60309-2

### Specifications

Housing	PBT
Contact Carrier	High-Impact Thermoset
Terminal Screws	Stainless Steel

### Performance

**Electrical**  
Current Interrupting Certified for current interruption at full rated current

Dielectric Voltage Withstands 3,000V AC  
Max Working Voltage 250V RMS


**Mechanical**  
Impact Resistance Per CSA C22.2 No. 182.1 / UL1682  
Product Identification Ratings are a permanent part of the device housing  
Terminal Identification Terminals identified in accordance with North American and IEC conventions

**Environmental**  
Flammability HB or better  
Ingress Protection IP22  
Operating Temperatures Max. Continuous +75°C; Min. -40°C w/o impact

### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

# HUBBELL



Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

