AV In-Wall Enclosure 15A, 125V

Recessed TR Duplex Receptacle

Features

- Tamper-Resistant (TR) duplex
- Easily mounts to a one gang box
- Back and side wiring

Ordering Information

Description	Device Color	UPC	Catalog Number
Smooth face, back and side	White	88377830572	RR1510W
wired.			

Listings

UL Listed to UL 498 CSA Certified 22.2, No. 42

Specifications

Face Nylon **PVC** Base **Power Contacts** .030 in. (.8mm) Brass **Ground Contacts** .014 in. (.35mm) Brass **Terminal Screws** Plated Steel Automatic Self-grounding Staple Stainless steel Mounting Screws Zinc Plated Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 1,500V minimum

Mechanical

Product Identification Ratings are a permanent part of the device

Terminal Accommodation #14-12 AWG stranded or solid copper conductor only Terminal Identification Terminals identified in accordance with UL 498 and CSA


Environmental

UL 94 V-2 Flammability

Maximum continuous 75°C; minimum -40°C (w/o impact) Operating Temperatures







Online Resources

Customer Use Drawing eCatalog Installation Instructions

