## Switches, Three Way 20A, 120-277V AC SNAPConnect® Heavy Duty Toggle Switches

# HUBBELL

#### **Features**

- Steel, zinc plated bridge is corrosion resistant
- Thread cleaning captive mounting screw
- Automatic self-grounding staple assures continuity to wall box

**Ordering Information** 

Description Toggle Color UPC Catalog Number SNAPConnect® White 783585189444 SNAP1223WNA Toggle

#### Listings

UL Listed CSA Certified Fed. Spec. W-S-896

**Specifications** 

Top Material Thermoplastic, Red
Base Material Thermoplastic, Black
Toggle Material Thermoplastic
Contacts Silver Alloy
Terminals Brass

### **Performance**

**Electrical** 

Dielectric Voltage Withstands 1500V AC minimum for 1 minute

Max. Continuous Current 20A Max. Working Voltage 277V AC

Overload Minimum 4.8 times rated current for 100 cycles

Temperature Rise 30°C maximum at rated current

Mechanical

Terminal Accommodations Uses SNAPConnect Connector


**Environmental** 

Flammability UL 94V-2

Operating Temperature Max. continuous: 75°C; Min. continuous: -40°C without

impact





#### **Online Resources**

Customer Use Drawing

eCatalog

Installation Instructions

