

Straight Blade Devices

15 Amp, 125 Volt, 2-Pole, 3-Wire

SNAPConnect® Extra Heavy Duty Receptacle



- Features
- Audible SNAP, indicates solid connection
  - Reduces installation time
  - Surge suppression, Tamper-Resistant, LED Indicator

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Surge Protection Receptacle	White	783585252032	SNAP5262WS

Listings


UL Listed to UL498 File No. E2410  
Certified to CSA, C22.2, No. 42 File 509  
Fed. Spec. W-C-820  
NEMA® WD-6 Compliant

Specifications

Face	Nylon
Base	Nylon
Line Contact	Brass
Ground Contact	Brass

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact)



Complementary Products

Wallplate or Weatherproof Cover  
Opening

Online Resources

Customer Sales Drawing  
eCatalog  
Installation Instructions

