

Straight Blade Devices

15 Amp, 125 Volt, 2-Pole, 3-Wire

inVIEW Illuminated Hospital Grade Devices

HUBBELL

Features

- Face LED Indicator
- Audible SNAP, indicates solid connection
- Reduces Installation Time
- Tamper-Resistant

Ordering Information

Description	UPC Number	Catalog Number
S-CONNECT DUP HG 15A/125V LED TR WH	783585250366	SNAP8200WLTR

Listings

UL
CSA

Specifications


Top	Polycarbonate
Base	Nylon
Contacts	Brass
Bridge	Galvanized Steel
Mounting Screws	Zinc Plated Steel

Performance

Electrical	Withstands 2,000V minimum Certified for current interrupting at full rated current
Mechanical	Ratings are a permanent part of the device
Environmental	UL 94V-2 Maximum continuous 75°C; minimum -40°C (w/o impact)



15A 125V AC
NEMA 5-15R
UL CSA
0.5 HP



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

