# Sensing Devices Passive Infrared Wall Switch Sensors




#### Features

- Nightlight version to provide illumination when the lights are OFF, neutral wire required
- Manual adjusting, auto ON operation
- Wallplate sold separately

## **Ordering Information**

**Description** Manual adjusting, auto ON operation; 120V AC only UPC Number Catalog Number 783585428192 WS1024NLA



## Listings

cULus listed to UL 773A

## Specifications

Housing Lens Dimensions

Mounting Height Mounting Strap Flame retardant UL 94 V-0 ABS Polyethylene Face 2.59"H x 1.30"W, 0.61"D (from wall out) 68 to 54 inches above floor Steel

## **Complementary Products**

Nylon Wallplate	NP26LA
SS Wallplate	SS26
Snap-On Wallplate	NPS26LA

## **Online Resources**

eCatalog

## Performance

**Controls** Front Press Switch Service Switch Time Delay

Electrical Load Capacity

**Environmental** Operating Temperature

Storage

6 seconds to 20 minutes (default set to 10 minutes) 120VAC, 600W Incandescent, 5A Ballast, 5A

CFL/LED, 277V; Horsepower rating 1/6

OFF (service); ON (normal operation)

32°F to 122°F (0°C to 50°C) with rate of change not exceeding 20°F(11°C) per hour -40°F to 150°F (-40°C to 65°C); 20% to 90% non condensing relative humidity

Sensing Indicators Passive Infrared

Red LED

ON/OFF

