Sensing Devices

Passive Infrared

Wall Switch Sensors

HUBBELL

Features

- Designed for use on 120V AC circuits, neutral wire required
- Manual adjusting, manual ON operation
- Wallplate sold separately

Ordering Information

Description Manual adjusting, manual ON operation; 120V AC only **UPC Number** 783585428307

Catalog Number WS1025I

Listings

cULus listed to UL 773A

Specifications

Housing Flame retardant UL 94 V-0 ABS


Lens Polyethylene

Dimensions Face 2.59"H x 1.30"W, 0.61"D (from wall

out)

Mounting Height 65 to 54 inches above floor

Steel Mounting Strap



Complementary Products

Nylon Wallplate NP26I SS Wallplate **SS26** Snap-On Wallplate NPS26I

Online Resources

eCatalog

Performance

Controls

Front Press Switch

Service Switch OFF (service); ON (normal operation) Time Delay

6 seconds to 20 minutes (default set to 10 minutes)

Electrical

Load Capacity 120VAC, 600W Incandescent, 5A Ballast, 5A CFL/LED, 277V; Horsepower rating 1/6

Environmental

Operating Temperature 32°F to 122°F (0°C to 50°C) with rate of change not

exceeding 20°F(11°C) per hour

Storage -40°F to 150°F (-40°C to 65°C); 20% to 90% non

condensing relative humidity

Sensing Indicators

Passive Infrared Red LED

