

WEEB-CCR-2, WEEB Top Clamp Washer, 1.59 IN L, 1.49 IN W , 0.33 IN hole size, Rigid

By WILEY

Catalog # [WEEB-CCR-2](#)



WEEB® Washer Electrical Equipment Bond.

Features

- Made from corrosion resistant 304 stainless steel for outstanding durability and performance
- Eliminates the need for surface preparation and oxide inhibitor
- Detailed manual specifying proper hardware, torque, and mounting information is available upon request
- UL467 Recognized for grounding and bonding equipment
- Custom grounding and bonding solutions available upon request

Application

WEEB washers offer a simple, low cost method to bond any non-conductive coated surfaces together reducing time, labor costs and the amount of copper wiring. WEEB's patented teeth pierce through most non-conductive coatings and embed into the underlying metal creating a bonding connection between the mounting surface and coated metal component that it is installed on or between.

General

Catalog Number	WEEB-CCR-2
Item Type	3C
Material	304 Stainless Steel
Trade Name	WEEB
UPC	781810668061
UPC 14 Digit GTIN	007818106680611

Dimensions

Dimension - Thread Size -

Certifications And Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	Y
Certification - cULus	N
Certified Listed	UL2703 Recognized
Industry Standard(s)	UL2703 Recognized
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	6000
-----------------	------

Product Assets

[Brochures - WEEB Washer Guide and WEEB Washer Theory](#)
[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)
[Certifications - Certificate of Compliance, UL 2703](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50038557](#)
[Specifications - WEEBCCR2](#)