



# ACC-ECTWA614, ACC-ECTW Clip with Cable Tie, 6/6 Nylon Cable Tie, 14" (360mm) Length, 3.94" (100mm) Max Bundle Diameter, Vertical/Parallel orientation, 3.0mm-6.0mm Flange Size

By WILEY  
Catalog # [ACC-ECTWA614](#)


ACC-ECTWA614, ACC-ECTW Clip with Cable Tie, 6/6 Nylon Cable Tie, 14" (360mm) Length, 3.94" (100mm) Max Bundle Diameter, Vertical/Parallel orientation, 3.0mm-6.0mm Flange Size

ACC-ECTs are nylon-encased clips with a steel tooth that grips the flange it is installed on. ACC-ECT Clips accommodate flanges between 1.3-3.0mm. The ACC-ECTW Clips accommodate flanges between 3.0-6.0mm. Clips come equipped with a cable tie pre-installed to route bundles either vertical/parallel (Style A) or horizontal/perpendicular (Style B) to the flange.

The cable tie is available in UV resistant, high impact, heat-stabilized nylon 6/6 or nylon 12 materials. Both versions have a tensile strength of 50 lbs. The nylon 12 version is especially suitable for high moisture, corrosive environments or where low temperatures are a factor.

## Features

- Route cable bundles without the need for mounting holes or additional hardware
- Installs in a vertical/parallel or horizontal/perpendicular orientation
- Steel lances securely anchor clips to module frames or purlins
- Offered in various nylon types with 50 lb tensile strength
- UV resistant, high impact stabilized Nylon 6/6



**Oh No!**  
IMAGE COMING SOON

- UV resistant, Nylon 12 which provides excellent UV, chemical and moisture resistance

## General

Catalog Number ACC-ECTWA614  
UPC 621945702028

## Logistics

Carton Quantity 1000

