

by Wiegmann

Catalog ID: WRD747218N4D3PT



* Representative image
NEMA 4 2-Door Floor Mount
Enclosure with Removable Pin Hinge
74X72X18 Carbon Steel - Gray

Designed to protect electrical components and instruments in typical industrial environments. Removable hinge pins reduce time and effort while removing enclosure doors, allowing access to internal components.

- Body and doors are fabricated from carbon steel
- Heavy-Duty 316 Stainless Steel Removable Hinge
- Seams are continuously welded and ground smooth
- 3-point keylocking/padlocking combo handle
- Doors are sealed with a poured in place gasket

Product Details

General

Color	Gray
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Floor Mount
Number of Doors (Fixed)	2
Series	Removable Pin Hinge
Type	Enclosure
UPC	786725889389

Dimensions

Actual Depth	22.85 in
Actual Height	89.26 in
Actual Width	72.13 in
Cubic Capacity	95904 cu.in
Depth	18
Height	74 in
Weight	595 lb
Width	72 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">cULusIEC 60950IP66
Nema Rating	3R, 4, 12 and IP66

```
$(document).on('click', '[data-toggle="lightbox"]', function(event) { event.preventDefault();  
$(this).ekkoLightbox(); });
```