



**WILEY-RLJ6C6-14, 6 IN L, 1/4 IN  
Hardware NOT included**

By WILEY

Catalog # [WILEY-RLJ6C6-14](#)

Wiley Rope-Lay Bonding Jumper; 1/4" Stud; 6" Length.



## Features

- Bond moving and stationary components with extremely flexible conductor stranding
- Standard mounting geometry and hardware requirements allow quick and easy installation
- Tin plated copper construction ensures durability against the elements and provides the environmental stability required for installation longevity
- Offered in a variety of lengths and mounting hardware sizes - customer configurations available upon request
- Listed to UL467 and UL2703

## General

Application	The Wiley Rope Lay Jumper is the optimal solution for bonding applications involving moving components. The WILEY-RLJ type jumpers are flexible in all directions and can be mounted to any flat surface. Made from tin plated copper stranding and crimped into a high-quality BURNDY lug, the rope lay jumper meets requirements of both UL467 and UL2703. At a size equivalent to #6 AWG conductor, engineers and installers can be confident in meeting or exceeding bonding requirements in most applications. The WILEY-RLJ jumpers are available with a variety of mounting hole sizes and in three standard lengths. Adding flexibility to both the installation process and application requirements, custom lengths and mounting configurations are available upon request.
UPC	621945553385

## Dimensions

Bolt Size	1/4 in
Length	6 in

## Conductor Related

Conductor Size	#6 AWG
----------------	--------

## Certifications And Compliance

Certified Listed	UL2703
Industry Standard(s)	UL2703

## Product Assets

[Catalog Page - BURNDY WileyRopeLayJumper CatCut](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Certifications - Certificate of Compliance, UL 2703](#)  
[Certifications - Certificate of Compliance, UL 467](#)  
[Sales Drawings - 50101194](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WLY-WILEYRLJ6C614-SPEC-EN | REV 6/2024