

by Wiegmann

Catalog ID: WRD90XM3920FS4



* Representative image
NEMA 4 1-Door Freestanding
Removable Pin Hinge Disconnect
90X39.5X20 Carbon Steel - Gray

Designed to protect electrical components and instruments in typical industrial environments. Removable hinge pins reduce time and effort while removing enclosure doors, allowing access to internal components.

- Body and door are fabricated from carbon steel
- Heavy-Duty 316 Stainless Steel Removable Hinge
- Seams are continuously welded and ground smooth. 3-point keylocking/padlocking combo handle
- Doors are sealed with a poured in place gasket. Back panels are included with this enclosure

Product Details

General

Color	Gray
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Series	Removable Pin Hinge
Type	Disconnect
UPC	786725889136

Dimensions

Actual Depth	20.13 in
Actual Height	90.13 in
Actual Width	39.38 in
Cubic Capacity	70200 cu.in
Depth	20 in
Height	90 in
Weight	505 lb
Width	39 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">cULusIEC 60950IP66
Nema Rating	3R, 4, 12 and IP66

```
$(document).on('click', '[data-toggle="lightbox"]', function(event) { event.preventDefault();  
$(this).ekkoLightbox(); });
```