

## Ground Fault Products

### Commercial Standard Hospital Grade GFCI Receptacles

# HUBBELL

#### Features

- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Protects against line and load reversal, no power to the face or downstream if device is miswired

#### Ordering Information

| Description  | Color | UPC         | Catalog Number |
|--|-------|-------------|----------------|
| 20A, 125V, Style Line®, hospital grade, AUTOGUARD® self test GFCI receptacle, flush face, back and side wired, multiple drive screws | Gray  | 88377899923 | GFR83GRY       |

#### Listings

UL Listed - Canadian and U.S.  
Meets ADA Standards  
Meets all NEC® requirements  
CSA Certified  
NEMA® WD-6 Compliant

#### Specifications

|                 |                   |
|-----------------|-------------------|
| Face            | Nylon             |
| Base            | Nylon             |
| Power Contacts  | Brass             |
| Ground Contacts | Brass             |
| Mounting Strap  | Brass             |
| Mounting Screws | Zinc plated steel |

#### Performance

##### Electrical

|                               |  |
|-------------------------------|--|
| Amperage                      | 20A, 20A Feed Thru                                       |
| Current Interrupting          | Certified for current interrupting at full rated current |
| Dielectric Voltage            | Withstands 1,500V minimum                                |
| Frequency                     | 60 Hz  |
| Maximum Interrupting Capacity | 10,000A  |
| Trip Level                    | 4 to 6 mA  |
| Trip Time                     | .025 second nominal                                      |
| Voltage                       | 120V AC +10% - 15% (102V to 132V)                        |

##### Mechanical

|                         |  |
|-------------------------|--|
| Product Identification  | Ratings are a permanent part of the device             |
| Terminal Accommodation  | #14-#10 AWG copper stranded or solid conductor only    |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA |

##### Environmental

|                       |                                 |
|-----------------------|---------------------------------|
| Flammability          | UL 94V-2                        |
| Operating Temperature | -35°C to 66°C or -30°F to 150°F |



#### Related Products

Wallplates for duplex openings

#### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

