

Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

Extra Heavy Duty Standard Duplex Receptacles
for Controlled Applications



- Features
- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
 - Patented TR design eliminates plug-in difficulty and TR complaints
 - Markings can be read regardless of mounting orientation
 - Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
 - Complements Hubbell's Load Logic control system or other available energy management system

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Finder Face, Duplex Receptacle	Brown	783585583709	HBL5262C1TR

Listings

UL Listed to UL498 File No. E2186
Certified to CSA, C22.2, No. 42 File 285
Fed. Spec. W-C-596
NEMA® WD-6 Compliant

Online Resources

[eCatalog](#)



Specifications

Face	Nylon
Base	PBT
Ground Contacts	.031 in. (.8) Brass
Clamping Plate	Plated steel
Mounting Strap	Brass
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc plated steel
By-Pass Power Contacts	.036 in. (.9) Brass

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-10 AWG stranded or solid copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)

