

Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

Extra Heavy Duty Standard Duplex Receptacles
for Controlled Applications



- Features
- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
 - Patented TR design eliminates plug-in difficulty and TR complaints
 - Markings can be read regardless of mounting orientation
 - Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
 - Complements Hubbell's Load Logic control system or other available energy management system

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Finder Face, Duplex Receptacle	White	783585583839	HBL5262C2WHITR

- Listings
- Fed. Spec. W-C-596
 - NEMA® WD-6 Compliant
 - UL Listed to UL498 File No. E2186
 - Certified to CSA, C22.2, No. 42 File 285

Specifications

Ground Contacts	.031 in. (.8) Brass
Clamping Plate	Plated steel
Mounting Strap	Brass
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc plated steel
Face	Nylon
Base	PBT
By-Pass Power Contacts	.036 in. (.9) Brass

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-10 AWG stranded or solid copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)



Online Resources

eCatalog

