


DB6 – Decorative Pole

TYPE

4" ROUND (RD) & FLUTED (FL) DECORATIVE BASE



DB6

1. BASE	2. POLE	3. OAH	4. COLOR	5. OPTIONS/ACCESSORIES				

1. BASE	2. POLE	3. OAH	SHAFT	WT	MAXIMUM ALLOWABLE EPA (MPH)									
					85	90	100	110	120	130	140	150		
DB6	4R10-125	10' (3.1m)	4" RD x .125"	50	19.4	17.1	13.5	10.8	8.9	7.4	6.3	5.5		
DB6	4R12-125	12' (3.7m)	4" RD x .125"	54	15.3	13.4	10.5	8.3	6.7	5.6	4.7	4.0		
DB6	4R14-125	14' (4.3m)	4" RD x .125"	57	12.3	10.7	8.2	6.3	5.0	4.1	3.4	2.9		
DB6	4R16-125	16' (4.9m)	4" RD x .125"	61	10.0	8.6	6.4	4.8	3.6	2.9	2.4	2.0		
DB6	4F10-188	10' (3.1m)	4" FL x .188"	56	22.1	19.5	15.4	12.4	10.2	8.5	7.1	6.1		
DB6	4F12-188	12' (3.7m)	4" FL x .188"	62	17.6	15.4	12.1	9.6	7.7	6.4	5.3	4.4		
DB6	4F14-188	14' (4.3m)	4" FL x .188"	67	14.3	12.5	9.6	7.5	5.9	4.8	3.9	3.2		
DB6	4F16-188	16' (4.9m)	4" FL x .188"	72	11.7	10.1	7.6	5.8	4.4	3.5	2.7	2.2		
DB6	4R10-226	10' (3.1m)	4" RD x .226"	60	23.8	21.0	16.7	13.5	11.1	9.3	8.0	6.9		
DB6	4R12-226	12' (3.7m)	4" RD x .226"	66	19.2	16.9	13.3	10.6	8.6	7.2	6.1	5.3		
DB6	4R14-226	14' (4.3m)	4" RD x .226"	73	15.9	13.9	10.8	8.4	6.8	5.6	4.7	4.0		
DB6	4R16-226	16' (4.9m)	4" RD x .226"	79	12.4	12.3	9.4	7.3	5.7	4.7	4.0	3.3		

Note: Overall height is measured to top of pole.

2. COLOR

BLS	Black Gloss Smooth
BLT	Black Matte Textured
DBS	Dark Bronze Gloss Smooth
DBT	Dark Bronze Matte Textured
GTT	Graphite Matte Textured
LGS	Light Grey Gloss Smooth
LGT	Light Grey Matte Textured
PSS	Platinum Silver Smooth
VGT	Verde Green Textured
WHS	White Gloss Smooth
WHT	White Matte Textured

Color Option

CC* Custom Color

* Consult factory for custom color, marine and corrosive finish options

3. OPTIONS / ACCESSORIES

- FH (Flag holder. Specify location on pole)
- FS1 (Single weatherproof fuse holder. Fuse by others.)
- FS2 (Double weatherproof fuse holder. Fuse by others.)
- LR (Ladder rest. Slips over a 4" O.D. pole.)
- PCA-T (Rotatable photocell housing. The housings slip over a 4"/100mm O.D. pole. A fixture slips over the 4"/100mm O.D. tenon. Includes an internal twist lock receptacle, and an access cover with integral lens and stainless steel tether. Adds 5"/125mm to the overall height of the pole/fixture assembly. Pre-wired on the load side and line side for easy installation. Photocell by others.)
- PCR (Low profile twist lock photocell receptacle with cast pole cap top. Secures to the top of the pole with three stainless steel set screws. Photocell by others.)
- PLT (Plant Hanger. For 4" O.D. poles. (specify location on pole)
- RBC (Cast aluminum receptacle housing, integrally welded to the pole. Includes a NEC approved clear weatherproof cover. Does not include a receptacle or internal wiring.)

SPECIFICATIONS

Base shall be cast aluminum #356 alloy, free of any porosity, foreign materials, or cosmetic fillers. Base casting shall be heat treated to a T-6 condition, and of uniform wall thickness, with no warping or mold shifting.

WARNINGS

Caution must be exercised in the selection of a design wind speed when the pole is to be installed in a special wind region (as indicated by the wind map) or in an area where wind speed is unpredictable.

AAL recommends consulting a local engineer when the pole is to be installed in an area that may be subject to extreme weather and exposure

Poles installed on structures such as buildings and bridges may be subjected to vibration, oscillations, and other fatigue effects which are not covered by the AAL warranty.

The use of banners or other appendages can severely affect the loading of a pole. No banner or other appendage should be attached to an AAL pole unless approved by AAL.

If the products are to be used on an existing foundation or on other structures, the customer assumes all responsibility for the structural integrity of the existing foundation, anchorage or structures and all the consequences arising therefrom.

CAUTION

Poles should never be erected without the luminaire installed.

Anchor bolts shall be hot dip galvanized steel. Eight galvanized hex nuts and flat washers, and a bolt circle template shall be provided. Anchor bolt for poles are 3/4" x 24" x 3".

CERTIFICATION

Certified UL 1598 in accordance with Article 410 of ANSI/NFPA 70, National Electrical Code.

JOB	_____
TYPE	_____
NOTES	_____



4" ROUND (RD) & FLUTED (FL) DECORATIVE BASE

DIMENSIONS

