

## Ordering Information

|                       |                            |                                      |
|-----------------------|----------------------------|--------------------------------------|
| <b>Color</b><br>Black | <b>UPC</b><br>783585022109 | <b>Catalog Number</b><br>HCTSP16PK12 |
|-----------------------|----------------------------|--------------------------------------|



## Specifications

|                    |                        |
|--------------------|------------------------|
| <b>Application</b> | Cable and Hose Carrier |
|--------------------|------------------------|

## Performance

### Environmental

|                                |   |
|--------------------------------|---|
| <b>Maximum Operating Speed</b> | 600 FPM (feet per minute), 180 MPM (meters per minute)  |
| <b>Operating Temperature</b>   | Continuous +20°F to +100°F (-7°C to 38°C);<br>Intermittent* -40°F to +220°F (-40°C to 104°C). |



## Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions