

Surge Protective Devices

20A 125V, 5-20R

SpikeShield® Specification Grade Isolated Ground Duplex Receptacle

Features

- IG triangle on the face of the receptacle clearly indicates isolated ground device on the face of the receptacle
- A “Clean” Path Provides A “Clean” Ground For Sensitive Equipment
- Power-on indicator light

Ordering Information

Description	Color	UPC	Catalog Number
Isolated ground, surge suppression duplex receptacles with light and alarm, 240 joules/15000A per mode.	Gray	783585060712	IG5362GYSA

Listings

CSA Certified to Specification C22.2 No. 42
Listed to UL Standards 498
UL Listed File E2186

Specifications

Application	Decorator Duplex with Light and Alarm
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Outlet	Straight Blade
Connectivity	Terminal Screws
Frequency Rating	60 Hz
Phase	Single Phase


Performance

Electrical	
Protection Modes	Normal and Common Modes
Response Time	Approximately 5 ns
Transient Suppression	Peak Energy (10 X 100 μs), Peak Current (8 X 20 μs)
Voltage	120V AC + 10% - 15%

Environmental

Flammability	UL 94V-2
Operating Temperature	32°F to 140°F (0°C to 60°C)

HUBBELL



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

