



Catalog Number	
Comments	

FEATURES

Application

The CRH Series offers emergency lighting for commercial applications. CRH works with Chicago approved products CCU2RC, CRURC and CLSC with remote capacity option.

Construction

The housing of the CRHI (Indoor Remote) is made of durable 20-gauge steel with a white finish. The housing of the CRHO (Outdoor Remote) is made of durable die-cast aluminum. CRHO is sealed and gasketed with a grey finish.

Installation

The CRH has an aluminum die cast universal mounting base for wall or ceiling mount.

Illumination

CRHI has 6V 5.3W LED lamp heads.
CRHO has 1 watt multi-volt LED lamp heads for use with 6V batteries.

Warranty

Full 5 year warranty



Indoor Remote Head - CRHI



Outdoor Remote Head - CRHO

ORDERING GUIDE

CRH

Model	Application	Heads
	1 Indoor	Blank Single
	0 Outdoor	2 Double

DIMENSIONS

