



Dynamo DYN Series

NEMA 4X / C1D2 / C2D1 Industrial LED Emergency Light

FEATURES

Application

The "Dynamo" DYN Series is a highly versatile superior lumen output, industrial application emergency lighting unit, designed to provide a minimum of 90 minutes illumination when primary power is lost. The DYN Series provides the same level of lumen output with no light degradation for the full 90 minutes of battery discharge. It has a flame-rated, UV stable thermoplastic housing which is fully gasketed and corrosion resistant with a gray finish. LED based lamp-heads are made of high strength die-cast aluminum with polycarbonate lens. Includes micro-controller based 3-stage charger and Lithium Iron Phosphate(LiFePO4) battery. The DYN Series accepts 120 through 277VAC input at 50 or 60Hz. Not designed for self-diagnostic operation at 220-240VAC input. Universal mounting plate made of painted stamped steel. The Dynamo is specifically designed for demanding environments, high reliability operation in industrial settings such as wet location or hose-down, food processing, food storage, production facilities, chemical plant and wastewater treatment. Hazardous location emergency lighting units with optional C1D2 listed for use in NEC Class I, Division 2, Groups A, B, C and D and Class 1, Zone 2, Groups IIA, IIB, IIB+H2, IIC. Hazardous Location Emergency Lighting Units with optional C2D1 listed for use in NEC Class II, Division 1, Groups E, F and G, and Zone 20, 21 and Class 3.

Construction

The DYN series housing, covers, remote housing and shield are made of polycarbonate. Lamp-heads are made of die-cast aluminum for thermal dissipation. LED lenses are made of polycarbonate. The Food Processing(FP) and Class 2, Division 1(C2D1) optioned DYN includes a clear polycarbonate shield which fully covers the lamp-heads.

Installation

The unit includes a universal mounting plate which facilitates mounting to a truss or I-beam, pole, column, or wall. Included is a special bracket to ensure positive pole gripping when using bands. In wet or NEMA 4X applications, use UL listed water tight conduit fittings that meet the requirements of the UL 514B Standard for Conduit Tubing and Cable Fittings when using knockouts on the side or top of unit. All fittings supplied by others. C1D2 and C2D1 listed models include 2 each hazardous location rated conduit hubs with ground provision.

Illumination

The DYN series provides bright and uniform illumination and is specifically designed for higher mounting heights above 9'. Coverage provided by 2 sealed aluminum lamp-heads using 3 high power LEDs each. The LEDs are located in a specially designed heat dissipating lamp-head which is fully adjustable and can be locked into position. The DYN is designed for full lumen output across the entire 90 minutes of operation. This ensures maximum visibility of the egress path over the full 90 minute discharge period.

Warranty

LED Lifetime Warranty
 DYN Standard Model- 3 Year Full
 DYN Spectron Model- 5 Year Full

Catalog Number	
Comments	Type



Patent Pending

ACCESSORIES

DYNRS-4X	NEMA 4X Rated Single Head Remote
DYNRD-4X	NEMA 4X Rated Double Head Remote
DYNRS-4X-FP	Food Processing rated Single Head Remote (Includes Polycarbonate Shield)
DYNRD-4X-FP	Food Processing rated Double Head Remote (Includes Polycarbonate Shield)
WGA2	Wire Guard (Does not include Food Processing option) 15"H x 14"L x 7"D
DYNRD-C1D2	Class 1, Div. 2 Remote, 3W heads, 1 conduit hub included
DYNRD-C2D1	Class 2, Div. 1 Remote, 3W heads with shield, 1 conduit hub included



Compliances

Listed to UL924 Standard, NFPA 101, NFPA 70
 Wet Location, NEMA 4, 4X rated
 UL Sanitation Certified with FP Option
 IP66 rated for 4X models only
 C1D2 and C2D1 optioned products;
 Listed to Standard 924 and Standard 844 (Hazardous Location)
 NEC Class 1 Division 2 Groups A, B, C, D
 NEC Class 2, Division 1 Groups E, F and G
 NEC Class 3
 CEC T20 Compliant

ORDERING GUIDE

DYN

Model	Capacity	Self-Diagnostics	Application	Lamp
	6 6 Watt ² 12 12 Watt ³	Blank I Wet Location Spectron® Self Diagnostics	Blank 4X Wet Location NEMA 4X/IP66 Rated FP Food Processing Rated ⁴ HTR Heater for Cold Temp ⁵ C1D2 Class 1 Div. 2 ⁶ C2D1 Class 2 Div. 1 ⁷	Blank 06L 3 Watt LED lamps 6 Watt LED lamps ¹

¹ Only available on DYN with 12 watt capacity

² DYN6 only available in the following configurations-DYN6, DYN6I, DYN6-4X, DYN6I-4X, DYN6I-4X-HTR, DYN6I-4X-FP, DYN6I-4X-HTR-FP

³ DYN12 only available in the following configurations-DYN12, DYN12I, DYN12-4X, DYN12I-4X, DYN12I-4X-FP, DYN12I-4X-HTR, DYN12I-4X-HTR-FP, DYN12I-4X-FP, DYN12I-4X-FP-06L, DYN12I-4X-FP-06L, DYN12I-4X-FP-06L, DYN12I-4X-FP-06L, DYN12I-4X-FP-06L, DYN12I-4X-FP-06L, DYN12I-4X-FP-06L, DYN12I-4X-FP-06L

⁴ FP option must be ordered with 4X option. Example: DYN6I-4X-FP

⁵ HTR option only available with Spectron®

⁶ C1D2 Option only available with DYN6I-C1D2, DYN12I-C1D2, and DYN12I-C1D2-06L

⁷ C2D1 Option only available with DYN6I-C2D1, DYN12I-C2D1, and DYN12I-C2D1-06L which includes shield





Dynamo DYN Series

NEMA 4X / C1D2 / C2D1 Industrial LED Emergency Light

SPECIFICATIONS

Additional Product Information

	Battery	Capacity	Lamp(W)	Lumens per Lamp	Remote Lamp Watts	Run-Time	Extended Runtime	Remote Capable	Remote Part Number
DYN6	LiFePO4	6 watts	3 watts	331	0	90 min	No	No	N/A
DYN6I	LiFePO4	6 watts	3 watts	331	0	90 min	No	No	N/A
DYN12	LiFePO4	12 watts	3 watts	331	6	90 min	Yes	Yes	DYNR
DYN12I	LiFePO4	12 watts	3 watts	331	6	90 min	Yes	Yes	DYNR
DYN12-06L	LiFePO4	12 watts	6 watts	514	0	90 min	No	No	N/A
DYN12I-06L	LiFePO4	12 watts	6 watts	514	0	90 min	No	No	N/A

Electronics

Upon failure of the normal utility power, a LED driver is automatically activated to power the emergency LED lamp-heads. At resumption of normal utility power, the LED driver is turned off. The battery is recharged through a micro-controller based 3-stage charger. The battery is a maintenance-free Lithium Iron Phosphate (LiFePO4) type. The EVHC series accepts dual-voltage input of 120 through 277VAC at 50 or 60 Hz. A low voltage battery disconnect(LVD) feature protects the battery from severe damage during prolonged power failures. Manual testing is available at any time using the push-to-test button. The optional heater features a heating wrap and thermostat to maintain optimal battery temperature during charge or discharge. The DYN remote can be located up to 100' from the source unit using 12 gage wire.

Number of Lamps: 2 lamp-heads with 3 high-power LEDs per head

Lamp Color: Cool White, 5000K

Total Lamp Output: Standard Model, 331 lumens per lamp-head

Optional 6W Lamps, 514 lumens per lamp-head

Rated LED Lifecycle: Greater than 100,000 hrs

Standard Features Include:

- Wet location operation with lock-down head positioning(no shield)
- Sealed external push-to-test switch and AC-on indicator
- Battery re-charge within 24 hours
- AC Lock-out circuit
- Low voltage battery disconnect
- Conduit entry knock-out located at the top center and upper half of each side
- Micro-controller based 3-stage charger
- Flashing service alert code for "Battery Disconnect" or "Charger Fault" in compliance with UL 924

Optional Feature Include:

- 4X -NEMA4, 4X option fully sealed and gasketed for indoor/outdoor use, splash and hose-down environments and corrosion resistance
- FP- Food processing option is UL Sanitation certified for use in food preparation and storage, and in food service establishments
- HTR- Includes a heating wrap and thermostat to maintain optimal battery temperature in cold environments to -22°F(-30°C)

Optional Spectron Includes:

- Self-diagnostics monitors LED status, LED driver circuit, battery capacity and charger function and displays any fault detection by means of a flashing code
- Self-Test feature automatically runs a 1 minute test once a month and an alternating 30-60 minute test once every 6 months. Multi-color LED indicator provides visible fault detection and charging status
- User initiated 1, or 90-minute system test feature
- 15 minute re-transfer delay
- Automatic unit transfer in brown-out conditions (below 80% of nominal AC input voltage)

INPUT POWER CONSUMPTION

	Input Voltage	Amps.	Max. Watts
DYN6	120	0.03	3.40
	277	0.04	3.49
DYN6 with heater	120	0.18	20.94
	277	0.08	21.13
DYN12	120	0.05	5.98
	277	0.04	6.52
DYN12 with heater	120	0.21	25.30
	277	0.09	25.60

Maintenance Mode Power Consumption 120VAC- 0.33W

Maintenance Mode Power Consumption 277VAC- 0.36W

Operating Temperature:

Wet/NEMA 4X Location Listed: 50° to 122°F(10° to 50°C)

Heater Option Models: -22° to 122°F(-30° to 50°C)

Temperature Codes and Maximum Temperature Ratings

Operating Temperature in °C			
Ambient °C	CLASS 1 DIV. 2 A, B, C, D	CLASS 2 DIV. 1 E, F, G	Supply Wire Temp. °C Min.
40	T6	T6	75
50	T5	T6	75


Photometrics available for download at www.dual-lite.com



Dynamo DYN Series

NEMA 4X / C1D2 / C2D1 Industrial LED Emergency Light

APPLICATION INFORMATION



* Multiple unit spacing based on 6' path

Industrial Parameters CH=30', R=10/10/10, Ceiling mounted (Multiple Unit Spacing), 6' Path															
DYN12-06L (6 watt lamp option)								DYN6 (3 watt lamps)							
Mounting Height	20'	18'	16'	14'	12'	10'	7.5'	Mounting Height	20'	18'	16'	14'	12'	10'	7.5'
Max Spacing @ 1 FC Avg	62'	65'	68'	71'	74'	77'	81'	Max Spacing @ 1 FC Avg	43'	45'	48'	51'	53'	56'	59'
Max Spacing @ 1 FC Min	35'	34'	34'	33'	32'	31'	29'	Max Spacing @ 1 FC Min	28'	28'	27'	27'	26'	24'	22'



Dynamo DYN Series

NEMA 4X / C1D2 / C2D1 Industrial LED Emergency Light

DIMENSIONS

