



POLE TOP BRACKETS	Cat.#		
	Job	Type	
			Approvals

ORDERING INFORMATION


TENON TYPE BRACKETS (STEEL)

(order as separate part #, field installed)


Catalog Number	Description	Max allowable load per tenon	Bracket EPA, MAX.	Bracket weight, MAX
BHB-2-180	Twin	100 lbs (45.5 kg)	0.9 ft ² (.08 m ²)	25 lbs (11.4 kg)
BHB-2H-180	Twin Horizontal	60 lbs (27.2 kg)	0.5 ft ² (.05 m ²)	25 lbs (11.4 kg)
BHB-3-180	3-in-line	100 lbs (45.5 kg)	1.5 ft ² (.14 m ²)	38 lbs (17.3 kg)
BHB-4-180	4-in-line	100 lbs (45.5 kg)	2.2 ft ² (.20 m ²)	51 lbs (23.2 kg)
BHB-3-120	3 @ 120	100 lbs (45.5 kg)	1.2 ft ² (.11 m ²)	40 lbs (18.2 kg)
BHB-4-90	4 @ 90	100 lbs (45.5 kg)	1.3 ft ² (.12 m ²)	41 lbs (18.2 kg)




BHB-2-180




BHB-3-180



BHB-3-120




BHB-4-90



BHB-4-180

A	B	C	D	E
16.5"	30"	25.8"	21.6"	9"
419 mm	762 mm	655 mm	549 mm	229 mm

2" PIPE (2-3/8" O.D.) TYPICAL



BHB-2H-180

ORDERING INFORMATION – ORDERING EXAMPLE: BHB-2-180-PT20-DB

BHB	-		-		-		-	
CONFIGURATION		POLE TENON SIZE		COLOR		OPTIONS		
2-180		PT20 2" pipe tenon (2.38" O.D.)		DB Dark bronze textured		BAS3 3" SLEEVE (For luminaires requiring a 3" slipfit)		
2H-180		PT25 2.5" pipe tenon (2.88" O.D.)		BL Black textured				
3-180		PT35 3.5" pipe tenon (4.0" O.D.)		WH White textured				
4-180				GR Gray textured				
3-120				PS Platinum silver smooth				
4-90				GYS Light gray smooth				
				BZT Bronze textured				
				BBT Basic black textured				



Beacon Products • 2041 58th Avenue Circle East Bradenton, FL 34203 • Phone: 800-345-4928

Due to our continued efforts to improve our products, product specifications are subject to change without notice.

© 2019 BEACON PRODUCTS, All Rights Reserved • For more information visit our website: www.beaconproducts.com • Printed in USA **POLEBRKTS-SPEC** JUNE 14, 2019 9:29 AM

