

Type:
 Job:

Fixture Catalog number:

Fixture Module and Finish

Hood and Finish

Mounting Options:

Ordered Separately from Fixture
 See page 2

Approvals:

Date:
 Page: 1 of 3

Specifications

Hood: Spun copper with low copper alloy aluminum die-cast reflector and hinge assembly. The hood is either raw copper or verde green patina and the reflector is always painted white. The hood reflector assembly is removable with a no-tool stainless steel snap latch. Hood is available in three styles: Pagoda, Cone, and Mushroom.

Husk: Die-cast brass with stainless steel hinge / latch assembly.

Globe: Fluted glass.

Stem: 20" schedule 40 red brass pipe with 1/2" NPT at bottom plus solid brass locknut for secure mounting.


Wiring: 3' No. 18-2 12 Volt cable with fork connectors.

Optical System: A total of 3 LED emitters configured in a rectangular array comprised together as a module. Available 3000K, 4200K, and 5100K.

Driver: Constant current electronic driver. Available in 12V input. -40°F. starting temperature. All drivers are Underwriters Laboratories recognized.

Finish: Natural Brass (**NB**) or Verde Green Patina (**VG**).

Certification: UL Listed to U.S. and Canadian safety standards for wet locations.



NOTE: Fixture modules and hoods may be ordered separately.



ORDERING INFORMATION

Fixture	Source	Finish
<input type="checkbox"/> KLV197/3L3K/NB	5.2W, 3 LED's, 3000K ¹	Brass/Natural
<input type="checkbox"/> KLV197/3L4K/NB	5.2W, 3 LED's, 4200K ¹	Brass/Natural
<input type="checkbox"/> KLV197/3L5K/NB	5.2W, 3 LED's, 5100K ¹	Brass/Natural
<input type="checkbox"/> KLV197/3L3K/VG	5.2W, 3 LED's, 3000K ¹	Brass/ Verde
<input type="checkbox"/> KLV197/3L4K/VG	5.2W, 3 LED's, 4200K ¹	Brass/ Verde
<input type="checkbox"/> KLV197/3L5K/VG	5.2W, 3 LED's, 5100K ¹	Brass/ Verde

¹ .43 Max Amps.



Pagoda Hood

Material / Finish

- H60NB Copper / Natural
- H60VG Copper / Verde Green Patina



Mushroom Hood

Material / Finish


- H70NB Copper / Natural
- H70VG Copper / Verde Green Patina



Cone Hood

Material / Finish

- H80NB Copper / Natural
- H80VG Copper / Verde Green Patina




KIM LIGHTING RESERVES THE RIGHT TO CHANGE SPECIFICATIONS WITHOUT NOTICE.

Type:

Job:

Page: 2 of 3



Mounting Options


Ordered Separately from Fixture

<p>Landscape Light Post by Engineered Products Co.</p> <p>Cat. No.</p> <p><input type="checkbox"/> EP17</p> <p><input type="checkbox"/> No Option</p>	<p>PVC fixture molded in black with 1/2" NPT mount is corrosion free and UV resistant. Replaces EMT, conduit connectors and weatherproof boxes. 100% shatter resistant against denting and cracking. Angled bottom to eliminate cable congestion.</p> <p>17 1/2" post length</p>	
<p>Low Voltage Spear Mount</p> <p>Cat. No. Finish</p> <p><input type="checkbox"/> KLV400BL Black</p> <p><input type="checkbox"/> KLV400DB Dark Bronze</p> <p><input type="checkbox"/> KLV400GR Verde Green</p> <p><input type="checkbox"/> No Option</p>	<p>Die-cast low copper aluminum with 1/2" NPSM fixture mount. Stainless steel set screw locks fixture into mount. Cable slot allows easy fixture mounting before or after installation in ground. Super TGIC powder coat paint over clear anodizing and titanated zirconium conversion coating.</p> <p>Spear Mounting in Concrete</p> <p>In addition to soil mounting, the KLV400 can be installed in a concrete footing for added stability and permanence.</p>	
<p>Low Voltage Surface Mount</p> <p>Cat. No. Finish</p> <p><input type="checkbox"/> KLV405BL Black</p> <p><input type="checkbox"/> KLV405DB Dark Bronze</p> <p><input type="checkbox"/> KLV405GR Verde Green</p> <p><input type="checkbox"/> No Option</p>	<p>Die-cast low copper aluminum with 1/2" NPSM fixture mount. Stainless steel set screw locks fixture into mount. Two holes provided for flat head wood screws. TGIC powder coat paint over clear anodizing and titanated zirconium conversion coating.</p>	
<p>Extension Module</p> <p>Cat. No. Finish</p> <p><input type="checkbox"/> KLV415BL Black</p> <p><input type="checkbox"/> KLV415DB Dark Bronze</p> <p><input type="checkbox"/> KLV415GR Verde Green</p> <p><input type="checkbox"/> No Option</p>	<p>For raising fixtures to a height above foliage for efficient and unobstructed operation. Constructed of 1 5/8" diameter extruded aluminum with die-cast ends. 1/2" NPSM female thread on one end, and other end has a 1/2" NPSM solid brass nipple. Stainless steel allen head set screw locks fixture onto mount. Super TGIC powder coat paint over titanated zirconium conversion coating. Two modules may be stacked for additional height.</p>	
<p>Transformer Options</p>	<p>See "12-15 Volt Variable Transformers" on kimlighting.com - Product Specifications - Landscape 12 Volt-120Volt section.</p>	

Type:

Job:

Page: 3 of 3



Lumen Data

Spectroradiometric			
	3000K	4200K	5100K
Correlated Color Temp. CCT (K)	2800 to 3175K	3800 to 4600K	4600 to 5600K
Color Rendering Index (CRI)	≥75	≥70	≥65

ELECTRICAL - Drive Current @350mA (3 LEDs)		
Volts	Amps	System Watts
12	0.43	5.2

Absolute Lumens (3 LEDs)	
Temperature	KLV197/3L*K
3000K	57.4
4200K	67.3
5100K	70.3

Lumens Per Watt (3 LEDs)	
Temperature	KLV197/3L*K
3000K	11.0
4200K	12.9
5100K	13.5