
#### Round Aluminum Non-Tapered Pole


kl\_pra\_spec.pdf


# **KIM**LIGHTING®


Type: **Approvals:** Job: **Catalog number:** Pole Optional Duplex Mounting Structural Luminiare Finish Optional Hinged Option Base Receptacle See page 3 See page 4 See page 2 Date: Page: 1 of 5

## **Specifications**









**Pole Construction:** Seamless round extruded aluminum tube of alloy 6061-T6, welded to top and bottom of aluminum base casting of alloy 356.

**Base Cover:** Base has a two-piece cast aluminum full cover of 319 alloy, secured by stainless steel screws.

**Pole Cap:** A flush-sided cast aluminum pole cap is provided for side arm mounted luminaires.

**Handhole:** 18" up from base, with a gasketed cover and ground lug.

**Anchor Bolts:** Four galvanized anchor bolts provided, complete with eight nuts, eight flat washers, and a presswood template.

**Vibration Dampener:** All poles 25' and above include an internally mounted, factory installed pendulum vibration dampener, with flush stainless steel socket head fasteners finished to match pole.

**Strength:** Poles will withstand wind loads as listed in chart (See page **2**) when luminaires are mounted per fixture installation instructions.

**Finish:** Durable thermoset polyester powder coat paint finish with nominal 3.0 mil thickness. Decorative finish coat available in multiple standard colors; Custom colors available, RAL number preferred.

**CAUTION:** Installation of poles without luminaire(s) will compromise pole strength. Any accessories attached to pole, or other modifications will compromise pole strength and may result in pole failure.

**Maintenance:** A regularly scheduled maintenance program must be established to insure the protective paint coating is intact, corrosion or structural damage has not occurred, and anchor bolt nuts are tight. Failure to do so could lead to pole collapse and serious personal injury.

**Certification:** Certified UL 1598 in accordance with Article 410 of ANSI/NFPA 70, National Electrical Code.



kl\_pra\_spec.pdf

Type:

Job: Page: 2 of 5

### **Standard Features**

**NOTE:** All allowable pole and fixture EPAs are derived from the AASHTO standard. Responsibility lies with the specifier for correct pole selection based on local codes and standards for the job location. (See page **4**).

Pole –	V	V							ind Ma Steady Wind	р
Catalog Number	Х	Υ	85	90	100	110	120	130	140	150
☐ PRA8-4	<b>125</b> 8'	4" x .125	13.06	11.49	10.46	8.39	6.81	5.65	4.80	4.13
☐ PRA8-5	<b>125</b> 8'	5" x .125	21.29	18.79	17.15	14.05	11.72	9.92	8.49	7.34
☐ PRA10-	<b>4125</b> 10'	4" x .125	9.78	8.53	9.09	7.01	5.42	4.30	3.58	3.01
☐ PRA10-	<b>5125</b> 10'	5" x .125	16.21	14.21	12.90	10.51	8.72	7.34	6.25	5.38
☐ PRA12-	<b>4125</b> 12'	4" x .125	7.48	6.44	5.75	4.37	3.32	2.59	2.14	1.78
☐ PRA12-	<b>5125</b> 12'	5" x .125	12.67	11.00	9.91	8.01	6.60	5.51	4.66	3.99
☐ PRA12-	<b>6188</b> 12'	6" x .188	32.89	29.22	27.04	22.20	18.53	15.69	13.44	11.64
X   PRA14-	<b>4125</b> 14'	4" x .125	5.73	4.84	4.25	3.06	2.16	1.57	1.24	0.98
☐ PRA14-	<b>4188</b> 14'	4" x .188	10.56	9.14	8.21	6.34	4.92	3.91	3.26	2.74
☐ PRA14-		5" x .125	10.01	8.58	7.64	6.10	4.98	4.11	3.44	2.91
☐ PRA14-	<b>5188</b> 14'	5" x .188	17.90	15.62	14.12	11.46	9.48	7.95	6.75	5.79
		6" x .188	27.19	24.11	22.37	18.31	15.24	12.87	11.00	9.49
☐ PRA16-		4" x .188	8.55	7.31	6.50	4.86	3.62	2.76	2.25	1.85
☐ PRA16-		5" x .125	7.90	6.65	5.83	4.57	3.67	2.98	2.45	2.03
☐ PRA16-		5 <b>"</b> x .188	14.80	12.81	11.50	9.26	7.61	6.34	5.34	4.55
☐ PRA16-	<b>6188</b> 16'	6" x .188	22.77	20.16	18.75	15.29	12.69	10.68	9.09	7.82
Handhole □ PRA20-	<b>4188</b> 19.5'	4" x .188	5.33	4.37	3.74	2.48	1.52	0.91	0.63	0.42
│	<b>5125</b> 19.5'	5" x .125	4.50	3.54	2.90	2.11	1.56	1.16	0.85	0.62
Base PRA20-	<b>5188</b> 19.5'	5" x .188	9.83	8.29	7.28	5.73	4.60	3.75	3.09	2.56
Cover PRA20-	<b>6188</b> 19.5'	6" x .188	15.69	13.81	12.95	10.46	8.59	7.16	6.03	5.14
☐ PRA25-	<b>6188</b> 25'	6" x .188	9.74	8.46	8.07	6.38	5.12	4.17	3.43	2.85
□   □   □   □   PRA30-	<b>6188</b> 30'	6" x .188	5.61	4.74	4.69	3.54	2.71	2.08	1.60	1.23
	<b>6250</b> 30'	6" x .250	11.37	9.88	9.42	7.45	5.99	4.88	4.02	3.34



kl\_pra\_spec.pdf

Type:		

Job: Page: 3 of 5

8 1/2"

10 1/2"

10 1/2"

**Anchor Base and Bolt Detail**\$

4"-5"

6<sup>11</sup>

6"

16'-20'

16'-20'

25'-30'

### **Standard Features**

**NOTE:** All allowable pole and fixture EPAs are derived from the AASHTO standard. Responsibility lies with the specifier for correct pole selection based on local codes and standards for the job location. (See page **5**).

3/4" x 30" + 4"

3/4" x 30" + 4"

3/4" x 30" + 4"


11 7/8 E"

14"

14"

3" dia. 5" dia.

5" dia.



Pole Height	Pole Diameter	Bolt Circle Dia.	Anchor Bolt Projection	Anchor Bolts Size	Base Cover Size	Conduit Opening
8 <b>'</b> -14 <b>'</b>	4"	8 1/2"	3 1/4"	3/4" x 15" + 3'	" 11 7/8"	3" dia.
8'-14'	5"	8 1/2"	3 1/4"	3/4" x $30$ " + 4"	" 11 7/8"	3" dia.
121	6"	10 1/2"	3 1/4"	3/4" x 30" + 4"	" 11 7/8"	3" dia.
14'	6"	10 1/2"	3 1/4"	3/4" x 30" + 4"	" 11 7/8"	3" dia.

3 1/4"

3 3/8"

3 3/8"

mount EPA. Please refer to Kim luminaire catalog for specific fixture.

<sup>1</sup>See luminaire drilling requirements in luminaire catalog.

#### Structural Luminaires Only - Examples

- ☐ **TS**:Single Tension for small and large Structural PRA20-5188SB-TS
- □ **TD**:Double Tension for small and large Structural PRA20-5188B-TD
- ☐ TR:Truss for small and large Structural PRA20-5188SB-TR
- □ XTS: Single Tension for 1000W Structural PRA20-5188B-XTS
- □ XTD: Double Tension for 1000W Structural PRA20-5188B-XTD
- □ **XTR**:Truss for 1000W Structural PRA20-5188B-XTR

Mounting



# Round Aluminum Non-Tapered Pole

kl\_pra\_spec.pdf

	M		G	H1	ΓIN	1G°
Ш		_				1

Туре:	
Job:	Page: 4 of 9


# **Standard and Optional Features**

Finish TGIC powder coat paint over a titanated zirconium conversion coating.	Cat. No.: Color:  BLS Black Gloss Smooth BLT Black Matte Textured DBS Dark Bronze Gloss Smo DBT Dark Bronze Matte Tex GTT Graphic Matte Textured Light Grey Gloss Smoot  Custom color subject to addit Consult representative. Custom	tured WHS  WHT  CC  ional charges, minir	Light Grey Matte Textu Platinum Silver Gloss S Verde Green Matte Tex White Gloss Smooth White Matte Textured Custom Color <sup>1</sup>	emooth extured extended lead times.		
Optional Hinged Base Cat. No.	Optional hinged base availab mount poles up to <b>14 feet</b> or bases requires some pre-plann the right direction, as dictate environment. <b>NOTE:</b> For <b>FM</b> mount, use <b>HB</b>	nly. The use of hing ing so poles hinge d by the surroundi	ged in	X1 $\uparrow$ $\rightarrow$ Y2 $\downarrow$ <b>A</b> mount  X2  X1 $\uparrow$ $\rightarrow$ Y2 $\downarrow$ B mount  X2		
Optional Duplex Receptacle Cat. No. DR DR-GFI No Option	Mounted opposite the handhole, at 22 <sup>8</sup> from base of pole, in a cast aluminum box the internally welded and sealed with a gasketed self-closing cover and locking bracket. <b>Duplex Receptacle (DR)</b> rated 20A., 125V. <b>Duplex Receptacle with Ground Fault Circuit Interrupter (DR-GFI)</b> rated 20A., 125V.					

kl\_pra\_spec.pdf

Type:

Job: Page: 5 of 5



#### **NOTES:**

- Values are based on 50 year mean recurrence interval 30<sup>th</sup> above grade.
- Hawaii has an 105 mph wind velocity.
- Puerto Rico has a **125 mph** wind velocity.
- Caution must be exercised in determining wind velocities in special wind areas such as:
  - Mountainous Regions
  - Areas surrounding the Great Lakes or other large bodies of water or open land.
  - Areas subject to extreme wind conditions, such as hurricanes, typhoons, cyclones, and tornadoes.
  - Areas adjacent to airports.
  - Any specific area with a known or suspected abnormally high intermittent wind condition caused by geography, adjacent structures, or other specific local conditions that may not be recorded in National Weather Service records
- Allowable pole EPA for jobsite wind conditions must be equal to or greater than fixture EPA. Responsibility lies with the specifier for correct pole selection based on AASHTO wind map and job location.

- The Wind Map is intended only as a general guide. Always consult local authorities to determine maximum wind velocities, gusting and unique wind conditions for each specific application.
- CAUTION: Wind speeds and listed EPAs are for ground mounted installations. Poles mounted on structures (such as bridges and buildings) must consider vibration and coefficient of height factors beyond this general guide. Consult AASHTO standards.
- Extreme Wind Events: Hurricanes, Typhoons, Cyclones, or Tornadoes expose poles to flying debris, wind shear, and other unpredictable aerodynamic forces not indicated by the wind velocity ratings.
- Pole Strength Limited Warranty: Standard, unmodified Kim lighting Poles installed as recommended, undamaged by corrosion, or lack of maintenance, shall withstand steady wind conditions as provided on page 2 (Allowable Pole EPA). Installation of poles without luminaires, or attachment of any unauthorized accessories to poles shall void this warranty.