


Type:
Job:
Catalog number:

Approvals:

Pole Cat. No.	Mounting	Structural Luminaire Option	Finish	Optional Duplex Receptacle Receptical
_____	See page 2	_____	_____	See page 4

Date:
Page: 1 of 4

Specifications



Pole Construction: One-piece non-tapered square shaft of low carbon steel (ASTM-A500, Grade B, 46,000 PSI min. yield) with one flush-welded vertical seam. Shaft is welded to a flat steel anchor base (ASTM-36, 36,000 PSI min. yield).

Base Cover: Base has a two-piece cast aluminum full cover of 319 alloy, secured by stainless steel screws.

Pole Cap: A flush-sided cast aluminum pole cap is provided for side arm mounted luminaires.

Handhole: 18" up from base, with a gasketed cover and ground lug. Reinforced 3" x 5" handhole is provided on poles 20' and taller.

Anchor Bolts: Four fully galvanized anchor bolts provided (ASTM-36, 36,000 PSI min. yield), complete with eight galvanized nuts, eight galvanized flat washers, and a presswood template.

Strength: Poles will withstand wind loads as listed in chart (see page 2) when luminaires are mounted per fixture installation instructions.

Finish: Super TGIC thermoset polyester powder coat paint, 2.5 mil nominal thickness.

CAUTION: Do not install poles without luminaires or strength guarantee is voided. Any unauthorized accessories secured to pole shall void strength guarantee.

Maintenance: A regularly scheduled maintenance program must be established to insure the protective paint coating is intact, corrosion or structural damage has not occurred, and anchor bolt nuts are tight. Failure to do so could lead to pole collapse and serious personal injury.


Certification: Certified UL 1598 in accordance with Article 410 of ANSI/NFPA 70, National Electrical Code.

Type:

Job:

Standard Features

NOTE: All allowable pole and fixture EPAs are derived from the AASHTO standard. Responsibility lies with the specifier for correct pole selection based on local codes and standards for the job location. (See page 4)



Pole TM Pole Catalog Number	X	Y	Allowable Pole EPA								Wind Map
			85	90	100	110	120	130	140	150	Steady Wind
<input type="checkbox"/> KSS10-4120	10'	4" x 11 ga.	28.7	25.3	20	16	13.06	10.71	8.85	7.33	
<input type="checkbox"/> KSS12-4120	12'	4" x 11 ga.	22.91	20.12	15.67	12.37	9.86	7.91	6.35	5.11	
<input type="checkbox"/> KSS14-4120	14'	4" x 11 ga.	18.66	16.22	12.4	9.57	7.42	5.75	4.42	3.35	
<input type="checkbox"/> KSS16-4120	16'	4" x 11 ga.	15.25	13.15	9.81	7.32	5.45	3.98	2.82	1.86	
<input type="checkbox"/> KSS20-4120	19.5'	4" x 11 ga.	10.42	8.73	6.05	4.06	2.6	1.43	0.51	---	
<input type="checkbox"/> KSS20-4180	19.5'	4" x 7 ga.	20.6	17.8	13.5	10.3	7.9	6	4.5	3.3	
<input type="checkbox"/> KSS25-4120	25'	4" x 11 ga.	5.05	3.8	1.82	0.38	---	---	---	---	
<input type="checkbox"/> KSS25-4180	25'	4" x 7 ga.	12.8	10.7	7.6	5.3	3.5	2.1	---	---	
<input type="checkbox"/> KSS25-5120	25'	5" x 11 ga.	9.1	7.35	4.52	2.35	0.71	---	---	---	
<input type="checkbox"/> KSS25-5180	25'	5" x 7 ga.	13.9	11.6	7.9	5.1	3	1.4	---	---	
<input type="checkbox"/> KSS30-4180	30'	4" x 7 ga.	5.9	4.7	2.5	1.1	---	---	---	---	
<input type="checkbox"/> KSS30-5180	30'	5" x 7 ga.	10.7	8.5	5.2	2.7	0.8	---	---	---	

Anchor Base and Bolt Detail

Pole Height	Pole Size	Bolt Circle DIA	Anchor Bolt Projection	Anchor Bolts Size	Base Cover Size	Conduit Opening
10'-16'	4"	7 1/2"-8 1/2"	3 3/8"	3/4" x 15" + 3"	8 5/8" sq.	3" SQ
20'-30'	4"	7 1/2"-8 1/2"	3 3/8"	3/4" x 30" + 3"	8 5/8" sq.	3" SQ
25'-30'	5"	10"-12 1/2"	3 7/8"	3/4" x 30" + 3"	12 5/8" sq.	3" SQ

Mounting

	Flush Mount	Post Top	Side Arm					
Plan Views:								
Mounting¹:	<input type="checkbox"/> FM	<input type="checkbox"/> PT	<input type="checkbox"/> A <input type="checkbox"/> SA	<input type="checkbox"/> B <input type="checkbox"/> SB	<input type="checkbox"/> L <input type="checkbox"/> SL	<input type="checkbox"/> T <input type="checkbox"/> ST	<input type="checkbox"/> C <input type="checkbox"/> SC	

NOTE: Allowable Pole EPA for jobsite wind conditions must be equal to or greater than fixture mount EPA. Please refer to Kim luminaire catalog for specific fixture.

¹See luminaire drilling requirements in luminaire catalog.†

Structural Luminaires *Only* - Examples

- TS:** Single Tension for small and large Structural - KSS20-4120B-TS
- TD:** Double Tension for small and large Structural - KSS20-4120B-TD
- TR:** Truss for small and large Structural - KSS20-4120B-TR
- XTS:** Single Tension for 1000W Structural - KSS20-4120B-XTS
- XTD:** Double Tension for 1000W Structural - KSS20-4120B-XTD
- XTR:** Truss for 1000W Structural - KSS20-4120B-XTR

Type:


Job:

Page: 3 of 4

Standard and Optional Features

<p>Finish Powder coat paint.</p>	<table border="0"> <tr> <td style="vertical-align: top;"> <p>Cat. No.: Color:</p> <p><input type="checkbox"/> BLS Black Gloss Smooth</p> <p><input type="checkbox"/> BLT Black Matte Textured</p> <p><input type="checkbox"/> DBS Dark Bronze Gloss Smooth</p> <p><input type="checkbox"/> DBT Dark Bronze Matte Textured</p> <p><input type="checkbox"/> GTT Graphic Matte Textured</p> <p><input type="checkbox"/> LGS Light Grey Gloss Smooth</p> </td> <td style="vertical-align: top;"> <p>Cat. No.: Color:</p> <p><input type="checkbox"/> LGT Light Grey Matte Textured</p> <p><input type="checkbox"/> PSS Platinum Silver Gloss Smooth</p> <p><input type="checkbox"/> VGT Verde Green Matte Textured</p> <p><input type="checkbox"/> WHS White Gloss Smooth</p> <p><input type="checkbox"/> WHT White Matte Textured</p> <p><input type="checkbox"/> CC Custom Color¹</p> </td> </tr> </table> <p>¹Custom color subject to additional charges, minimum quantities and extended lead times. Consult representative. Custom color description: _____</p>	<p>Cat. No.: Color:</p> <p><input type="checkbox"/> BLS Black Gloss Smooth</p> <p><input type="checkbox"/> BLT Black Matte Textured</p> <p><input type="checkbox"/> DBS Dark Bronze Gloss Smooth</p> <p><input type="checkbox"/> DBT Dark Bronze Matte Textured</p> <p><input type="checkbox"/> GTT Graphic Matte Textured</p> <p><input type="checkbox"/> LGS Light Grey Gloss Smooth</p>	<p>Cat. No.: Color:</p> <p><input type="checkbox"/> LGT Light Grey Matte Textured</p> <p><input type="checkbox"/> PSS Platinum Silver Gloss Smooth</p> <p><input type="checkbox"/> VGT Verde Green Matte Textured</p> <p><input type="checkbox"/> WHS White Gloss Smooth</p> <p><input type="checkbox"/> WHT White Matte Textured</p> <p><input type="checkbox"/> CC Custom Color¹</p>
<p>Cat. No.: Color:</p> <p><input type="checkbox"/> BLS Black Gloss Smooth</p> <p><input type="checkbox"/> BLT Black Matte Textured</p> <p><input type="checkbox"/> DBS Dark Bronze Gloss Smooth</p> <p><input type="checkbox"/> DBT Dark Bronze Matte Textured</p> <p><input type="checkbox"/> GTT Graphic Matte Textured</p> <p><input type="checkbox"/> LGS Light Grey Gloss Smooth</p>	<p>Cat. No.: Color:</p> <p><input type="checkbox"/> LGT Light Grey Matte Textured</p> <p><input type="checkbox"/> PSS Platinum Silver Gloss Smooth</p> <p><input type="checkbox"/> VGT Verde Green Matte Textured</p> <p><input type="checkbox"/> WHS White Gloss Smooth</p> <p><input type="checkbox"/> WHT White Matte Textured</p> <p><input type="checkbox"/> CC Custom Color¹</p>		
<p>Optional Duplex Receptacle Cat. No. <input type="checkbox"/> DR <input type="checkbox"/> DR-GFI <input type="checkbox"/> No Option</p>	<p>Mounted opposite the handhole, at 22 1/2" from base of pole, in a cast aluminum box that is internally welded and sealed with a gasketed self-closing cover and locking bracket.</p> <p>Duplex Receptacle (DR) rated 20A., 125V.</p> <p>Duplex Receptacle with Ground Fault Circuit Interrupter (DR-GFI) rated 20A., 125V.</p>		

Type:
 Job:



Wind Map

United States and Canada

To obtain more information on AASHTO Standards for Lighting Equipment contact:

American Association of State Highway and Transportation Officials:
 444 N. Capitol Street, NW,
 Suite 249
 Washington, DC 20001
 (202) 624-5800
www.aashto.org

NOTES:

- Values are based on 50 year mean recurrence interval 30' above grade.
- Hawaii has an **105 mph** wind velocity.
- Puerto Rico has a **125 mph** wind velocity.
- Caution must be exercised in determining wind velocities in special wind areas such as:
 - Mountainous Regions
 - Areas surrounding the Great Lakes or other large bodies of water or open land.
 - Areas subject to extreme wind conditions, such as hurricanes, typhoons, cyclones, and tornadoes.
 - Areas adjacent to airports.
 - Any specific area with a known or suspected abnormally high intermittent wind condition caused by geography, adjacent structures, or other specific local conditions that may not be recorded in National Weather Service records.
- Allowable pole EPA for jobsite wind conditions must be equal to or greater than fixture EPA. Responsibility lies with the specifier for correct pole selection based on AASHTO wind map and job location.
- The Wind Map is intended only as a general guide. Always consult local authorities to determine maximum wind velocities, gusting and unique wind conditions for each specific application.
- **CAUTION:** Wind speeds and listed EPAs are for ground mounted installations. Poles mounted on structures (such as bridges and buildings) must consider vibration and coefficient of height factors beyond this general guide. Consult AASHTO standards.
- Extreme Wind Events: Hurricanes, Typhoons, Cyclones, or Tornadoes expose poles to flying debris, wind shear, and other unpredictable aerodynamic forces not indicated by the wind velocity ratings.
- Pole Strength Limited Warranty: Standard, unmodified Kim lighting Poles installed as recommended, undamaged by corrosion, or lack of maintenance, shall withstand steady wind conditions as provided on page 2 (Allowable Pole EPA). Installation of poles without luminaires, or attachment of any unauthorized accessories to poles shall void this warranty.