

Type:
Job:
Catalog number:




Approvals:

LED Kit / /
Electrical Module Option


Date:
Page: 1 of 4

Specifications

LE26-LED-KIT
120 Light Emitting Diodes



Driver Assembly



LED EmitterDeck®

Electronic Module: All electrical components are UL recognized, mounted on a single plate and factory prewired with quick-disconnect plugs. Module includes a driver, LifeShield® temperature control device and surge protector. Electrical module attaches to housing with no-tool hinges and latches, accessible by opening the lens frame only. Driver is rated for -40°F starting and has a 0-10V dimming interface for multi-level illumination options.

Optical Module: Precision, replaceable PicoEmitters™ are positioned to achieve directional control toward desired task. The entire EmitterDeck fastens to the housing as a one-piece module.

NOTE: Existing product conditions are taken as the base point. Participation rules apply. See complete warranty provisions for further details.

IMPORTANT: Disable all power to the luminaire before conducting any maintenance or upgrade activity. Failure to do so will create a hazardous working environment.

Listed To: UL 1598 Standard for Luminaires - UL 8750 Standard for Safety for Light Emitting Diode (LED) Equipment for use in Lighting Products and CSA C22.2#250.0 Luminaires.

CAUTION: Fixtures must be grounded in accordance with national, state and/or local electrical codes. Failure to do so may result in serious personal injury.

Suggested Tools:

- Flat Blade Screwdriver

Type:

Job:

Page: 2 of 4



Standard Features

Fixture

Cat. No. designates fixture and distribution

LE26-LED-KIT

Upgrade Kit:

- ☐ LET26-LED-KIT
☐ LEB26-LED-KIT


Distribution:

- ☐ 1 = Type I ☐ 4 = Type IV
☐ 2 = Type II ☐ 5 = Type V
☐ 3 = Type III
☐ R = Type R Right ☐ L = Type L Left

E35

E35 = 350mA

Light Distribution:



TYPE I



TYPE II



TYPE III



TYPE IV



TYPE V



TYPE R
One-Way Right



TYPE L
One-Way Left

Electrical Module

Cat. Nos. for Electrical Modules available:

120L

Source:

120L = 120 LED's

xK

Color Temperature:

- ☐ 2K = 580nm - Amber
☐ 3K = 3000K
☐ 4K = 4200K
☐ 5K = 5100K

x

Voltage:

- ☐ 120 = 120V
☐ 208 = 208V
☐ 240 = 240V
☐ 277 = 277V
☐ 347 = 347V¹
☐ 480 = 480V¹

¹Due to current unavailability of 347V and 480V drivers, specification of these voltages may feature an integral step-down transformer.

Kim Lighting reserves the right to change specifications without notice.

Type:

Job:


Page: 3 of 4



Standard Features

0-10V Dimming Interface

Driver has a 0-10V dimming interface with a dimming range of 10-100%. Is compatible with most control systems including Hubbell Building Automation w-HUBB™. Approved dimmers include Lutron Diva AVTV, Lutron Nova NFTV and NTFTV. Note: Not compatible with current sourcing dimmers. Controls compatible via Gray and Purple dimming lead.




Optional Feature

Fusing

Cat. No. (See right)
☐ No Option

High temperature fuse holders factory installed inside the fixture housing.

Line Volts:	120V	208V	240V	277V	347V	480V
Cat. No.:	<input type="checkbox"/> SF	<input type="checkbox"/> DF	<input type="checkbox"/> DF	<input type="checkbox"/> SF	<input type="checkbox"/> SF	<input type="checkbox"/> DF



Single Fuse

Type:

Job:

Page: 4 of 4



Lumen Performance Charts

Spectroradiometric			
	3000K Average	4200K Average	5100K Average
Correlated Color Temp. CCT (K)	2800K - 3175K	3800K - 4600K	4600K - 5600K
Color Rendering Index (CRI)	80≤	80≤	≤70
Power Factor	>.90	>.90	>.90

Projected Lumen Maintenance*		
mA	100,000 hrs	Calculated L70
350 mA	92.80%	543,000 hrs.

Electrical Drive Current		
350mA		
Volts - AC	Amps - AC	System Watts
120	1.05	126
208	0.61	126
240	0.53	126
277	0.45	126
347	0.36	126
480	0.26	126

B.U.G. Rating for 350mA (TM15) in Lumens where B = Backlight, U = Uplight, G = Glare								
Temperature	Type I	Type II	Type III	Type III NFO	Type IV	Type IV NFO	Type V	Type L/R
3000K	TBD	B2 U0 G2	B2 U0 G2	N/A	B1 U0 G2	B1 U0 G2	B3 U0 G1	TBD
4200K	TBD	B3 U0 G3	B2 U0 G2	N/A	B1 U0 G2	B1 U0 G2	B3 U0 G1	TBD
5100K	TBD	B3 U0 G3	B2 U0 G2	N/A	B2 U0 G2	B1 U0 G2	B3 U0 G2	TBD

Absolute Lumens for 350mA								
Temperature	Type I	Type II	Type III	Type III NFO	Type IV	Type IV NFO	Type V	Type L/R
3000K	TBD	6993	6884	N/A	6538	5515	6943	TBD
4200K	TBD	8949	8809	N/A	8687	7058	8885	TBD
5100K	TBD	9685	9534	N/A	9056	7638	9616	TBD

LED performance and lumen output continues to improve at a rapid pace. Log onto www.kimlighting.com to download the most current photometric files from Kim Lighting's IES File Library.
For custom optics and color temperature configurations, contact factory.
*Data is prorated from 5000K IES files.

Kim Lighting reserves the right to change specifications without notice.