

New and Existing Construction

LB6 & LBEB6

LED Downlight Module 10W High Efficacy Wet Location 120V

DATE:	TYPE:	
FIRM NAME:		
PROJECT:		











Sheet for ceiling cutout requirements Not to Scale

APPLICATIONS:

LiteBox LED modules are designed for use in new construction as well as retrofit applications with existing Prescolite or competitive 6" housings using the included screw base adapter. Lumen output and distribution comparable to a 65W BR30 while consuming only 10 watts. ENERGY STAR® qualified. Can be used to comply with California Title 24 Commercial and IECC watts per square foot requirements. Suitable for use with continuous room side ambient temperature up to 25°C. Continuous dimming to 10% with most standard dimmers. (See Dimming Notes).

LIGHT ENGINE:

High efficacy LED light engine, available in 2700K, 3000K, 3500K and 4000K. 120VAC, 50/60Hz, with output overvoltage, over-current, and short circuit protection. System designed for optimal life and lumen maintenance (60,000 hours at 70% lumen maintenance per TM-21).

LENS/REFLECTOR:

All LiteBox LED modules are provided standard with a diffused optical grade, impact resistant polycarbonate lens for uniform illumination and superior glare control. Reflector powder coat finish creates aesthetic ceiling appearance and visually comfortable cutoff.

INSTALLATION:

For New Construction: Use with Prescolite DBX QuickLink LED housings. QuickLink connector mates directly to housing connector without a screw base adapter for compliance to California Title 24 non-screw base socket requirement.

For Retrofit: Use in Prescolite or other compatible 6" recessed housings using supplied screw base adapter.


Easy installation with (3) stainless steel spring clips (pre-installed).


CERTIFICATIONS:

cCSAus Classified for use in Prescolite or other 6" recessed housings including Halo, Juno, and Lithonia. (See page 3 for more details) Suitable for wet locations. ENERGY STAR qualified. Can be used to meet California Title 24 commercial with DBXQL.

WARRANTY:

5 year warranty Additional information on pg 3. See www.prescolite.com for details.





CATALOG NUMBER: EXAMPLE: LB6A7L30K9 WH

TRIM	OUTPUT	ССТ	CRI	TRIM COLOR	- ACCESSORIES
□ LB6A 6" LiteBox Downlight LED Module with dimming to 10% 120V □ LBEB6A³ 6" LiteBox Adjustable LED Module with dimming to 10% 120V	□ 7L 700 Lumens	□ 27K 2700 Kelvin □ 30K 3000 Kelvin □ 35K 3500 Kelvin □ 40K ² 4000 Kelvin	9 90+ CRI	□ WH White	□ LiteGear¹ Inverter, single phase central lighting, 125VA-250 □ LPS Series¹ LitePower micro-inverter, 20VA-55VA □ DBXQL IC/Non-IC Airtight housing with supply wire quick connects
					NOTES
					See Central Inverter compatibility note and web links on page 3
					2 Not available with IBER6




3 Damp location only

PHOTOMETRIC DATA

Litebox LED - 6" LED Downlight Module

ELECTRICAL DATA	6"
Input Voltage	120V AC
Input Frequency	50/60 Hz
Input Current	0.08A
Input Power	9.7W
Power Factor	>0.90
THD	<20%
EMI Filtering	FCC 47CFR
	Part 15, Class B
Operating Temperature	-30°C to 25°C
Dimming	Yes*

Over-voltage, over-current, short-circuit protected




INITIAL FOOTCANDLES (fc) DATA CHART

LB6A7L30K9 WH											
	5	Single Unit, fc	on 3	0" Work Plar	ne .			Multiple Units, av	erage fc c	n 30" Wo	ork Plane
0° (nadir)		10°		20° 30°		Ceiling		RCR 2	RCR 5	RCR 7	
fc	fc	Illuminated Diameter (feet)	fc	Illuminated Diameter (feet)	iameter fc Diameter		to Floor Height (feet)	Fixture Spacing (feet)	fc	otcandles	(fc)
12	11	2	8	4	6	6	8	6 x 6	18	13	11
8	8	2	6	5	4	8	9	7 x 7	13	9	8
6	5	3	4	6	3	9	10.5	9 x 9	8	6	5
5	5	3	4	6	2	10	11	9 x 9	7	5	4

^{*}Spacing to Mounting Height ratio 1.1

LB6A7L30K9 WH

LED Light Engine: 3000K 90 CRI System Wattage: 9.7W Fixture delivered lumens: 666 Fixture Efficacy: 68.4 Spacing Criteria: 1.1



CANDELA DISTRIBUTION DEG CANDELA								
0	353							
5	350							
15	326							
25	284							
35	231							
45	1 <i>75</i>							
55	101							
65	27							
75	9							
85	3							
90	0							

ZONAL LUMEN SUMMARY								
ZONE	LUMENS	%LUMINAIRE						
0-30	255	38.4						
0-40	400	60.1						
0-60	624	93. <i>7</i>						
0-90	666	100.0						

COEFFICIENTS OF UTILIZATION

Zonal Cavity Method

Zonai Cavily Memoa											
	% Effective Ceiling Cavity Reflectance										
iły		8	0%		70 %		50%		30%		
Ca		20% Effective Floor Cavity Reflectance									
Room Cavity Ratio		% Wall Reflectance									
Ro	70	50	30	10	70	10	50	30	50	30	
1	111	108	104	101	109	100	101	99	97	95	
3	96	87	80	75	93	74	82	77	80	75	
3 5 7	82	71	63	57	80	57	68	62	66	60	
	71	59	51	46	70	46	57	50	56		
9	62	50	43	38	61	38	49	42	48	42	


LB6A7L30K9 WH Test No. 17.00241

Test No.17.00241

Tested at 25°C Ambient in accordance to IESNA LM-79-2008

LBEB6A7L30K9 WH

LED Light Engine: 3000K 90 CRI System Wattage: 10.2W Fixture delivered lumens: 722 Fixture Efficacy: 70.8 Spacing Criteria: 1.1



CANDELA DISTRIBUTION						
DEG	CANDELA					
0	383					
5	380					
15	355					
25	304					
35	232					
45	155					
55	96					
65	55					
<i>75</i>	27					
85	9					
90	4					

ZONAL LUMEN SUMMARY								
ZONE	LUMENS	%LUMINAIRE						
0-30	275	38.1						
0-40	420	58.2						
0-60	626	86.7						
0-90	<i>7</i> 21	99.8						

COEFFICIENTS OF UTILIZATION

Zonal Cavity Method

		-	% Effe	ctive (Ceiling	Cavit	y Refl	ectar	ice		
≟		8	0%		70)%	50)%	30)%	
Ğ.e	20% Effective Floor Cavity Reflectance										
Room Cavity Ratio	% Wall Reflectance										
Ro	70	50	30	10	70	10	50	30	50	30	
1	110	106	102	99	108	97	100	97	96	93	
3	94	85	77	72	91	71	80	74	77	73	
5	81	69	61	55	79	55	66	59	64	58	
7	70	58	50	44	68	44	55	49	54	48	
9	62	49	42	36	60	36	47	41	46	40	
I RFR	A7130	K9 W	Н		•		To	t No	17.0	02/3	

Test No.17.00243

Tested at 25°C Ambient in accordance to IESNA LM-79-2008





^{*}See Dimming Notes for more information

Litebox LED - 6" LED Downlight Module

Central Inverters

For full fixture output in back-up mode, we recommend you visit www.dual-lite.com for your Central Lighting Inverter options. Please contact your local Hubbell representative for any assistance with proper sizing and loading of your inverter selection. Central lighting inverters must be ordered separately.

LiteGear: www.dual-lite.com/products/litegear lg_series

LPS Series: www.dual-lite.com/products/lps

DIMMING NOTES:

Prescolite's recessed LED modules are designed to be compatible with many dimmer controls. Electronic low-voltage rated dimmer controls may offer favorable dimming performance. Incandescent type dimmers are not recommended. The following is a list of known compatible dimmer controls:

<u>Manufacturer</u>	Series	Part Number	Dimmer Type
Lutron	Nova T	NTELV-300	ELV
Lutron	Spacer	SPSELV-600	ELV
Lutron	Maestro	MAELV-600	ELV
Lutron	Diva	DVELV-300P	ELV
Leviton	Decora SureSlide	6672-1LW	LED, CFL
Leviton	SureSlide	6615-P	ELV
Leviton	Renoir	AWRMG-EAW	ELV
Pass & Seymour	Harmony	DCL453PTCCCV6	LED, CFL

Incandescent Digital type dimmers are not recommended.

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are tradenames or registered trademarks of each respective company.

COMPATIBILITY OF 6" RECESSED HOUSINGS:


LiteBox LED modules are cCSAus classified for use with Prescolite and most competitive recessed cans (with "A" and "B" dimensions) including:

Prescolite

Capri

Commercial Electric

Elco
Emerald
Progress
Halo
Intense
Jimway
Juno
Lithonia
Lumapro
Luminaire



NOTES

- 1. Operation in ambient temperatures higher than those specified will shorten life and void warranty.
- 2. Warranty is limited to repair and replacement of defective parts of the LED system and does not include labor or installation. See www.prescolite.com for details.



