



FEATURES

- Attractive fluorescent architectural recessed luminaire
- Precision optical design produces high efficiency in a high visual comfort architecturally styled direct/indirect distribution
- Available for use with T8, T5 or T5HO linear fluorescent lamps
- Custom perforated metal basket is backed by a high transmission lamp-obscuring overlay
- Optimized coating process and unique paint formulation provide exceptional reflectivity in a matte finish for a soft visual image and balanced basket and reflector illumination
- Completely recessed, provides a clean ceiling with uniform illumination at mounting heights as low as 8 feet
- Optional acrylic dust guard pivots to seal lamp compartment against contaminants especially for schools, medical facilities and public spaces
- Recessed, surface or cable mount

PROJECT INFORMATION

Project Name _____

Type _____

Catalog No. _____

Date _____

CONSTRUCTION

Luminaire housing and end caps are die formed code gauge cold rolled steel. The sturdy reflector is stiffened with linear forms, profiled to a precision curve. Perforated basket with high transmission overlay for improved optical efficiency plus lamp obscuration. Basket and all reflective surfaces are finished after fabrication with unique formula high reflectivity matte white paint for soft, uniform indirect illumination.

Thermoplastic light traps snap into the housing at both ends of the basket to prevent light leaks. Basket hinges down for easy access to center wireway

INSTALLATION

An access plate is furnished with each recessed fixture for fast wiring connections without the necessity to open the fixture or wireway.

BALLASTS

Energy efficient, thermally protected, automatic resetting, Class P, high power factor, sound rated A, magnetic or electronic ballasts. CEE NEMA Premium compliant. Fixtures with two ballasts or emergency-equipped fixtures may require using end wireway access.

ELECTRICAL

Standard class "P", thermally protected, autoresetting HPF ballast, sound rated A. CEE NEMA Premium compliant. All ballast leads extend a minimum of 6" through access location. NEC/CEC-compliant ballast disconnect is standard.

CEILING COMPATIBILITY

Designed for recessed installation in standard inverted tee grid ceilings (G), recessed installation in hard ceilings (G with FK accessory), surface mount at ceiling plane (SM) or cable mount suspension below ceiling plane (CM). For type SG ceilings order G trim. Fixture will be recessed 3/8" from the face of the ceiling tee. For compatibility with specific ceilings contact your Hubbell Lighting representative. Four integral T-bar clips are located in the end caps. Contact your Columbia representative for compatibility information for specific ceiling types or for continuous row applications in hard ceilings.

CERTIFICATION

All luminaires are built to UL 1598 standards and bear appropriate UL and cUL or CSA labels. Damp location labeling is standard. Emergency-equipped fixtures labeled UL 924.

ORDERING INFORMATION

EXAMPLE STE22-317G-MPO-EU

STE	22	3		MPO			
MODEL		NO. OF LAMPS		SHIELDING		VOLTAGE	OPTIONS
STE Stratus® E-Series Recessed Indirect		3 Three	CEILING TYPE	MPO Metal Perf w/Overlay		U 120V-277V 347 347V	C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex EL Emergency Battery Pack, 350-450 Lumens DG Dust Guard Clear Acrylic GLR Fast Blow Fuse GMF Slow Blow Fuse CP Chicago Plenum
	SIZE		LAMP TYPE		BALLAST		
	22 2' x 2'		14 2', T5: 14 Watt 17 2', T8: 17 Watt 24 2', T5HO: 24 Watt		E Electronic T8, Instant Start ED Electronic Dimming T8 and T5 EP Electronic T5, T5HO, or T8, Programmed Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T5, T5HO, Instant or T8 Programmed Start		
ACCESSORIES (ORDER SEPARATELY)							
FK22 2' x 2' Single Flange Kit (Shipped separately)							
FKCR Flange Kit Row Adapter							
CM 48Y25C3F 48" Cable Mount Kit for 2' wide Cable Mount Fixtures, 2 Wire							

¹ For drywall, order Flange Kit accessories separately.

² Order hanger accessories separately

PHOTOMETRIC DATA

Test 3485 Test Date 9/17/10

LUMINAIRE DATA

Luminaire	STE22-317G-MPO-3EU Stratus, Recessed/Architectural 2 x 2 2-lamp with perforated metal basket and opal overlay
Ballast	ICN-3P32-SC
Ballast Factor	0.92
Lamp	F17T8
Lumens per Lamp	1325
Watts	42
Shielding Angle	N/A
Spacing Criterion	0° = 1.20 90° = 1.31
Luminous Opening in Feet	Length: 1.92 Width: 1.92 Height: 0.00

ZONAL LUMEN SUMMARY

Zone	Lumens	% Lamp	% Fixt.
0-30	716	18.0	26.7
0-40	1173	29.5	43.7
0-60	2095	52.7	78.1
0-90	2684	67.5	100.0
0-180	2684	67.5	100.0

ENERGY DATA

Total Luminaire Efficiency	67.5%
Luminaire Efficacy Rating (LER)	59
IESNA RP-1-1993 Compliance	Noncompliant
Comparative Yearly Lighting Energy Cost per 1000 Lumens	\$4.07 based on 3000 hrs. and \$0.08 per KWH


COEFFICIENTS OF UTILIZATION (%)

RCR	RC	80				70				50				0
		70	50	30	10	70	50	30	10	50	30	10	0	
1	73	70	67	64	71	69	66	63	66	63	61	56		
2	67	61	56	52	65	60	55	52	57	54	50	47		
3	61	53	48	43	59	52	47	43	50	46	42	39		
4	55	47	41	37	54	46	41	36	45	40	36	33		
5	51	42	36	31	49	41	36	31	40	35	31	29		
6	47	38	32	27	46	37	31	27	36	31	27	25		
7	44	34	28	24	42	34	28	24	33	28	24	22		
8	40	31	25	21	39	31	25	21	30	25	21	20		
9	38	29	23	19	37	28	23	19	27	23	19	18		
10	35	26	21	17	35	26	21	17	25	21	17	16		

RCR = Room Cavity Ratio

RC = Effective Ceiling Cavity Reflectance RW = Wall Reflectance

INDOOR CANDELA PLOT




0.0 ——— 45.0 - - - - - 90.0 - - - - -

AVG. LUMINANCE (Candela/Sq. M.)


Average Luminance Angle	0.0	22.5	45.0	67.5	90.0
0	2689	2689	2689	2689	2689
30	2508	2539	2633	2711	2748
40	2359	2424	2584	2741	2798
45	2271	2362	2573	2767	2837
50	2162	2285	2548	2798	2889
55	2046	2204	2530	2836	2953
60	1904	2114	2517	2867	3008
65	1748	2004	2487	2847	2999
70	1579	1878	2416	2715	2740
75	1410	1692	2132	2437	2584
80	1127	1412	1833	2068	2136
85	905	1072	1374	1508	1541

DIMENSIONAL DATA




Top View

Surface K.O. Dimensions
A: 2" x 3" Access with (2) 7/8" Mount Supply Knockouts




CEILING COMPATIBILITY

Type G Side




For lay-in installation in exposed grid ceilings. Maximum tee widths of 1" and maximum heights of 1 1/2" allowed.

Type SG Ceiling



For 3/8" slot grid type ceilings. Luminaire will be regressed 3/8" horizontal surface of the tee.

FK Flange Kit




For hard ceiling applications, fixtures must be ordered with a flange kit that wires directly into the concealed ceiling opening for a clean finished appearance. For row configurations contact your local Columbia Representative.

Flange kit cut out dimension for single FK22 only: 24 3/8" x 24 3/8"

NOTE: All dimensions are in inches; dimensions and specifications are subject to change without notice. Please consult factory or check sample for verification.

DIMENSIONAL DATA - SURFACE OR CABLE MOUNT



NOTE: All dimensions are in inches; dimensions and specifications are subject to change without notice. Please consult factory or check sample for verification.

SURFACE MOUNT

Order SM ceiling type. Mounting collar required for surface mounting. (4) Mounting knock outs, 1/4" to 1/2" provided as shown, marked "A".

CABLE MOUNT

Order CM ceiling type. Access plate supplied for cable mounting or suspension. Use CM48Y2C3F-KIT 48" cable mount kit. Includes 3 wire feed cord. For other wiring needs, contact Hubbell representative. Mounting knock-outs, 1/4" to 1/2", provided as shown, marked "A".