



32L-C-P-D


Inde-Pendant Pendant Direct

Fixture Type:

Project Name:

Ordering Guide

Feature	Code	Options	Description
Series		32L	Inde-Pendant
Configuration		C	Cylinder
Mounting		P	Pendant
Fixture distribution		D	Direct
Primary Finish		C1 C4 C5 CC	Matte White (Default) Machined Aluminum Carbon Black Custom Color
Accent Finish		/AC1 /AC4 /AC5 /ACC	Matte Finish (Default) Machined Aluminum Carbon Black Custom Color
Color temperature		30K 35K 40K	3000K 3500K 4000K
Cylinder Direct Output <i>(specifiable in 50 lumens increments)</i>		D060 D300	600 3000
Driver		NDM D01 LEC LTW DALI	Non Dimming 1% Dimming, 0-10V Hi-lume 1% EcoSystem LED driver Hi-lume 1% 2-wire LED driver(120V forward phase only) DALI
Circuiting		1C	1 Circuit
Voltage		UNV 120 347	Universal Voltage (120-277) 120 Volt* 347 Volt** *LTW only **Excludes D01, DALI and Lutron Dimming Options
Ceiling Type		GDW PT OC	Grid or Drywall (Default) Plaster Trim Open Ceiling
Suspension kit		FA5 FA6 FA7	Suspension Kit, 48" (Default) Suspension Kit, 120" Suspension Kit, 240"
Canopy Color		/C1 /C4 /C5 /CC	Matte White (Default) Machined Aluminum Carbon Black Custom Color
Optional Features	Code	Options	Description
Chicago Environmental Air Modification		CCEA	Chicago Environmental Air Modification



Key Features

- Variable Intensity technology provides specifiable lumen output/wattage
- 2.5 SDCM color variation
- Remote-mounted driver assembly
- Customizable finish variations

Details

Construction:

Driver enclosure (GDW & PT)- Die formed steel. Canopy assembly contains die cast aluminum housing with steel canopy fascia plate that secures to housing using neodymium magnets. Canopy contains nylon bushings as power over aircraft isolation.

6" Ceiling depth required for driver installation.

Cylinder- Die cast aluminum cylinders containing nylon bushings as power over aircraft isolation.

Downlight diffuser:

Cylinder- Inner lens is soft diffuse acrylic.

Cylinder Outer lens is clear acrylic.

Finish/Color:

Visit www.litecontrol.com/finishes for details.

CCT:


30K-3000K output multiplier (0.97)

35K-3500K output multiplier (1.00)

40K-4000K output multiplier (1.02)

*All photometric files below based off 3500K. Any deviation from this color temperature is subject to have lumen output altered by multiplier shown.

Ex. 2000 lm x .97=1940 lm in 3000K.



Color Variation:

2 step MacAdam ellipse

Driver Lumen Output Ranges:

Direct

D01 or NDM: D060-D300

LHI or LEC: D080-D300

DALI: D060-D300

LTW: D080-D300

347V: D110-D300

Output (VI technology):

Variable Intensity (VI) technology allows precise specification of fixture output/wattage. Fixture will be programmed and labeled to specification.

Specify each in 50 lumen increments/ft within the below range:

Lumens	Nomenclature
Cylinder Direct	
Min: 600	D060
Max: 3000	D300

Driver:

NDM: Non-dimming. Fixture will be wired for fixed light output.

D01: 100%-1% dimming range. Fixture will be wired for low voltage 0-10V dimming control.

DS1: Soft-Start 100%-1% dimming range. Fixture will be wired for low voltage 0-10V dimming control.

D00: Dim-to-off 100%-1% Dimming range. Fixture will be wired for low voltage 0-10V dimming

DS0: Soft-Start Dim-to-off 100%-1% dimming range. Fixture will be wired for low voltage 0-10V dimming control.

LEC: Hi-Lume 1% EcoSystem LED Driver with Soft-on, Fade-to-Black dimming technology

LTW: Lutron Hi-Lume 2-wire dimming using Lutron A-Series driver

DALI: DALI compatible

*See driver limitations in Driver lumen output ranges section below.

Field Accessibility:

LED drivers and light engines can be accessed and removed from below ceiling. Contact factory for details.

Circuiting:

1C (1 Circuit) Fixture wired for a single circuit.

Suspension Kit:

Class 2 power over aircraft cable, 1/16" diameter field-adjustable. Ship separately installed with driver enclosed.

Rated Life (LED Board):

Tested in accordance to LM79-2008 & derived from EPA TM-21 calculator
L70: >54,000 hours (reported per TM21/LM80 6x limitations)

Rated Life (Driver):

100,000 hours

Fixture Weight:

4 lbs.

Ratings:

CSA listed for damp locations. IBEW. AF of L.

Warranty:

LED boards- 5 years


LED drivers (standard)- 5 years

LED drivers (Lutron)- 3 years

Planning for Installation:

Minimum distance of 12" between ceiling plane and cylinder to ensure access into driver enclosure.

*For complete details, reference Installation Instructions at Litecontrol.com.




Details (continued)

Color Characteristics:


Value	30K	35K	40K
Rf	81	84	81
Rg	98	96	97
CCT (K)	3104	3435	3911
Duv	-0.004	0.0016	0.0017
x	0.4353	0.4108	0.3857
y	0.4025	0.3973	0.3837
CIE Ra	81	83	81

Spectral Distribution:




Color Vector Graphic:


30K:




35K:



40K:



Color Gamut/Fidelity Plot:



CRI:

80 minimum

CCT	CRI	R1	R2	R3	R4	R5	R6	R7	R8	R9	R10	R11	R12	R13	R14
30K	81	79	88	97	80	80	87	82	57	0	74	80	73	80	98
35K	83	81	90	96	82	82	87	85	63	9	76	81	67	83	98
40K	81	79	86	93	82	80	83	85	63	2	69	82	67	80	96




Photometry

Fixture: 32L-C-P-D-CX/CX-30K-D185
 CCT: 3000K
 Output: D185
 Nominal lumens: 1850 lumens/ft
 Efficacy: 91.3 lm/W
 Test report: 32L-C-P-D-CX/CX-30K-D185.IES

Zonal Lumens

Zone	Lumens	Lamp %
0-40	1521	80.5%
0-60	1736	91.9%
0-90	1878	99.5%
90-180	10	0.5%
0-180	1889	100.0%



Performance- Cylinder Direct

Nomenclature	Lumens/unit	W/unit	Efficacy
D060	600	7.7	78
D065	650	8.1	80
D070	700	8.6	82
D075	750	9.0	84
D080	800	9.4	85
D085	850	9.8	87
D090	900	10.2	88
D095	950	10.7	89
D100	1000	11.1	90
D105	1050	11.5	91
D110	1100	11.9	92
D115	1150	12.4	93
D120	1200	12.8	94
D125	1250	13.2	95
D130	1300	13.6	95
D135	1350	14.2	95
D140	1400	14.7	95
D145	1450	15.3	95
D150	1500	15.8	95
D155	1550	16.4	95
D160	1600	16.9	95
D165	1650	17.5	95
D170	1700	18.0	94
D175	1750	18.6	94
D180	1800	19.1	94
D185	1850	19.7	94
D190	1900	20.2	94
D195	1950	20.8	94
D200	2000	21.4	93
D205	2050	22.1	93
D210	2100	22.8	92
D215	2150	23.4	92
D220	2200	24.1	91
D225	2250	24.7	91
D230	2300	25.4	91
D235	2350	26.0	90
D240	2400	26.6	90
D245	2450	27.2	90
D250	2500	27.8	90
D255	2550	28.4	90
D260	2600	28.8	90
D265	2650	29.2	91
D270	2700	29.6	91
D275	2750	30.0	92
D280	2800	30.4	92
D285	2850	30.8	92
D290	2900	31.2	93
D295	2950	31.6	93
D300	3000	32.5	92

(wattage may vary up to 5% from published)