



By Burndy
Catalog # [KA2U](#)

Aluminum Universal Terminal, 1 Hole, 14-2 AWG (Str), 1/4" Stud, 1 Screw, Al/Cu Rated, Tin Plated



Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

Application

For Aluminum And Copper Conductors

Specifications

EU RoHS Indicator	Yes
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - UL Listed Direct Burial	No

Conductor

Conductor - Nominal Diameter	0.072, 0.091, 0.116, 0.130, 0.146, 0.164, 0.184, 0.184, 0.184, 0.184, 0.184, 0.206, 0.232, 0.232, 0.260, 0.260, 0.292, 0.320
Number Of Conductors	1
Conductor - Copper Str Size Range	14-2
Conductor Type	CU C Str-Size;AL C Str-Size
Conductor - AL Str Size	8;6;4;3;2
Conductor - AL Str Size Range	8-2

Configuration

Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm
Dimension - Pad Width inch	0.51 in
Dimension - Height fraction	14/25 in
Dimension - Height inch	0.56 in
Dimension - Height mm	14.2 mm
Dimension - Bolt Hole Size inch	0.25 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - Stud Size inch	1/4
Dimension - D inch	0.63 in
Dimension - N inch	0.31 in
Dimension - Width fraction	1/2 in

Force Related

Installation Torque Recommended in-lb	50 LBS/in
---------------------------------------	-----------

General

Sub Brand	UNIVERSAL TERM
Material - Hardware	Steel
Physical Attribute - Screw Type	Slot
Type	Bolted Lugs & Terminals
UPC 14 Digit GTIN	00781810370056
Material	Aluminum
UPC	781810370056

Logistics

Carton Quantity	1600
-----------------	------

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)