

## Industrial Grade, Motor Disconnect, Unfused, 3 Pole, 30A 600V AC, Screw Terminals, IP69k, NEMA Type 4X, 12 Non- Metallic Sloped Top Enclosure, AC1 Aux Contact, inTOUCH Installation Free LED Phase Indication

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS30PAC](#)

Industrial Grade, Motor Disconnect, Unfused, 3 Pole, 30A 600V AC, Screw Terminals, IP69k, NEMA Type 4X, 12 Non-Metallic Sloped Top Enclosure, AC1 Aux Contact, inTOUCH Installation Free LED Phase Indication

### Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection and Certified by NSF for hygiene in food processing applications
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Product rating are permanently laser-marked and will not wash off
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Six highly visible integral phase identification LEDs for use on 3 Phase Y or Delta systems provide secondary means of visual confirmation of make/break on all phases

### Application

Heavy Duty Industrial and/or Washdown

### Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage, Electrical - Dielectric Voltage - Withstands 3000V AC minimum, Electrical - Max. Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and VO Classification, Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact, Environmental - UV Resistance - All materials are UV stabilized, Mechanical - Impact Resistance - In accordance with UL 746C, Mechanical - Mounting - Non-Metallic - External fully adjustable feet, Mechanical - Product Identification - Identification and ratings are part of external label, Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

### Specifications



Industry Standard(s)	cULus Listed
Environmental Conditions	Indoor and Outdoor
<b>Conductor</b>	
Wire Size	#14 AWG to #8AWG
<b>Configuration</b>	
Mounting Method	External fully adjustable feet
<b>Current</b>	
Dielectric Strength	Withstands 3000V AC minimum
Current / Amperage Rating	30 A
<b>Dimensions</b>	
Hub Size	3/4"
Weight	2.9 lb.
Height	4.12 in
<b>General</b>	
Material - Mounting Hardware	Stainless Steel Screw Mounting
Type	Disconnect Switches
Enclosure Type	IP69k and UL Type 4X, 12
Series	Non-Fused
Specifications	<ul style="list-style-type: none"> <li>• Base - Valox®</li> <li>• Enclosure Gasket - Neoprene</li> <li>• Handle - Valox®</li> <li>• Shaft (Unfused) - Valox®</li> <li>• Top - Valox®</li> </ul>
UPC	783585763057
Ingress Protection	IP69k, NEMA Type 4X, 12
Style	Heavy Duty
Color	Gray
<b>Operational</b>	
Operating Cycles	10,000 Cycles Minimum

Operating Temperature	Without Impact Maximum continuous 75°C and minimum -40 °C
Horsepower—Maximum	15

#### Product Assets

[Catalog Page \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved  
WDK-HBLDS30PAC-SPEC-EN | REV 1/2026