

**Industrial Grade, Motor  
Disconnect,Unfused,3 Pole, 30A 600V  
AC,Screw Terminals, IP69k,NEMA Type  
4X,12 Non-Metallic Sloped Top Enclosure,  
inTOUCH Installation Free LED Phase  
Indication,Jog**

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS30PJ](#)

Industrial Grade, Motor Disconnect,Unfused,3 Pole, 30A 600V  
AC,Screw Terminals, IP69k,NEMA Type 4X,12, Non-Metallic  
Sloped Top Enclosure, inTOUCH Installation Free LED Phase  
Indication,Jog

**Features**

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection and Certified by NSF for hygiene in food processing applications
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Product rating are permanently laser-marked and will not wash off
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Six highly visible integral phase identification LEDs for use on 3 Phase Y or Delta systems provide secondary means of visual confirmation of make/break on all phases

**Application**

Heavy Duty Industrial and/or Washdown

**Performance**

Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage, Electrical - Dielectric Voltage - Withstands 3000V AC minimum, Electrical - Max. Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and VO Classification, Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact, Environmental - UV Resistance - All materials are UV stabilized, Mechanical - Impact Resistance - In accordance with UL 746C, Mechanical - Mounting - Non-Metallic - External fully adjustable feet, Mechanical - Product Identification - Identification and ratings are part of external label, Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

**Specifications**



Industry Standard(s)  
Environmental Conditions

cULus Listed  
Indoor and Outdoor

**Conductor**

Wire Size #14 AWG to #8AWG

**Configuration**

Mounting Method External fully adjustable feet

**Current**

Dielectric Strength Withstands 3000V AC minimum  
Current / Amperage Rating 30 A

**Dimensions**

Hub Size 3/4"  
Weight 2.9 lb.  
Height 4.12 in

**General**

Material - Mounting Hardware Stainless Steel Screw Mounting  
Type Disconnect Switches  
Enclosure Type IP69k and UL Type 4X, 12  
Series Non-Fused  
Specifications

- Base - Valox®
- Enclosure Gasket - Neoprene
- Handle - Valox®
- Shaft (Unfused) - Valox®
- Top - Valox®

UPC 783585763125  
Ingress Protection IP69k, NEMA Type 4X, 12  
Style Heavy Duty  
Color Gray

**Operational**

Operating Cycles 10,000 Cycles Minimum

Operating Temperature	Without Impact Maximum continuous 75°C and minimum -40 °C
Horsepower—Maximum	15

#### Product Assets

[Catalog Page \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved  
WDK-HBLDS30PJ-SPEC-EN | REV 1/2026