Approvals

INTENDED USAGE

· Perimeter lighting for safety and security. Use on factories, warehouses, self storage, commercial buildings, etc.


CONSTRUCTION


- · Borosilicate glass refractor softens lamp image and provides uniform distribution - 4 times spacing to mounting height.
- Cast aluminum frame holds lens and seals to housing gasket with two stainless steel screws.
- · Door assembly hinges to side on mid-size units; hinges down on large units
- Cast aluminum housing with 1/2" conduit entries, button photocontrol can be field installed
- All units have dark bronze powder paint finish, Quad-Tap® ballasts and lamps included

ELECTRICAL


• WGH mid-size is 150w HPS/PS and 84w CFL; large size handles 250-400w PS and HPS; 150P unit includes medium base lamp; All other HID units include mogul base lamp




















Listed to UL1598 for use in wet locations

ORDERING INFORMATION

Ond Linia iii					
Catalog Number ¹	Wattage/Source	Voltage	Finish	Weight	
				lbs	kg
		MID-SIZE SERIES			
WGH-150P	150w/PS	120, 208, 240, 277V	Bronze	19	8.6
WGH-150S120	150w/HPS	120V	Bronze	15	6.8
		LARGE SERIES			
WGH-250P	250w/PS	120, 208, 240, 277V	Bronze	34	15.4

¹ Lamp included on all units

ACCESSORIES

(order as separate part #)

Catalog Number	Description	
PBT-1	Photocontrol, 120 volt	
PBT-234	Photocontrol, 208, 240, 277 volt	
SM106-SHIELD	Polycarbonate Shield for MID-SIZE fixtures	
SM106VISOR	Top visor for MID-SIZE fixtures	
SM708VISOR	Top visor for LARGE fixtures	

PHOTOMETRIC REPORTS

Catalog Number	Papart #
Catalog Nullibel	Report #
WGH150S	HP09709.IES
WGH400S	HP09706.IES