



REVISIONS


NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI
5. UL 1561
6. CSA -C22.2 No 47



PRIMARY VOLTS	%	CONNECT LEADS TO TAP NO.
504	105	1
492	102.5	2
480	100	3
468	97.5	4
456	95	5

PRIMARY LINES TO H1-H2-H3,
SECONDARY LINES TO X0-X1-X2-X3
CAUTION: KEEP 3 TAP CONNECTIONS IN SAME POSITION WHEN TRANSFORMER IS IN OPERATION



KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.



KVA	CATALOG NUMBER	VOLTAGE		WEIGHT	PHASE	FREQUENCY	
		HIGH	LOW				
112.5	H3112K0014BCS	480Δ	208Y/120	938 Lbs	3φ	60Hz	
Temp Rise:	130°C	TYPICAL PERFORMANCE DATA				Typical Efficiency @ 35%	
Insulation:	220°C	Regulation @ 100% PF		Windings:	CU	Typical No Load Losses:	
NEMA ST20 Standard:	50 dB	Standards:	UL/CSA	Impedance:		100% Load (Typ) Load Losses (I ² R)	
Electrostatic Shield:	YES	Approvals:	DOE-2016	Enclosure:	3R	Total Load Losses:	

DATE: 19-Oct-16

TYPE NO:

CASE 3

Meets US DOE 2016 Efficiency