




SIDE




BACK (1)



BACK (2)



Primary Volts	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
480	H1-H4	H2 to H3	
240	H1-H3 & H2-H4		
Secondary Volts			
240		X2 to X3	X1-X4
120/240		X2 to X3	X1-X2-X4
120		X1 to X3 X2 to X4	X1-X4



BOTTOM

ACME ELECTRIC

Type No.

KVA	CATALOG NUMBER	VOLTAGE		WIRING DIAGRAM	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
2.0	T-2-53012-SS	240 x	120/240		38 Lbs	1φ	60 Hz

Winding Rise	115°C
Insulation	180°C
Sound Level	40 dB

TYPICAL PERFORMANCE DATA

Regulation @
100% PF

IMPEDANCE

Typical
Efficiency

Full Load Losses

No Load Losses

316 - STAINLESS STEEL

A	B	C	D	E	F	G	H	J	K
12.52	5.40	5.13	1.67	4.92	11.68	5.50	9.03	13.00	1.50

A

PRINTS
TO

CONTROL
7