


CATALOG NUMBER	PHASE	FREQ.	MAX VOLTAGE	MAX AMPS	INDUCTANCE (uH / COIL) $\pm 10\%$	RESISTANCE @20°C (mΩ/COIL)	INS. SYS(°C)	WATTS LOSS 115% 60Hz 20°C	WDG. MATL.	WEIGHT
ALRB200CBC	3	60Hz	600	200	110	0.638	180	325	Cu	55 LBS.

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.

A	N/A	RELEASED	AJP	AJP	4-23-14
REV	ECO	DESCRIPTION	BY	ENG	DATE
BRAND					
UNLESS OTHERWISE SPECIFIED:					
TOLERANCES:		DRAWN	AJP	4-23-14	 <p>Acme Electric MENOMONEE FALLS, WI 53051 USA</p>
FRACTIONAL $\pm 1/64$		CHECKED	AJP	4-23-14	
IN X.XXX $\pm .005$ X.XX $\pm .01$ X.X $\pm .1$		ENG APPR.	AJP	4-23-14	
ANGULAR: $\pm .5^\circ$		SCALE: 1:4		TITLE: LINE REACTOR 200A	
MATERIAL: --		SHEET 1 OF 1		SIZE B	DWG. NO. ALRB200CBC
FINISH: --		DO NOT SCALE DRAWING		REV A	