






Revisions



BOTTOM

Primary Volts	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
600	H1, H2, H3	1	
570	H1, H2, H3	2	
540	H1, H2, H3	3	

Secondary Volts			
480			X1, X2, X3
277 1 phase			X1 to X0 X2 to X0 X3 to X0

NOTES:

- KNOCKOUTS:**
1.69 DIA. FOR 1.25 CONDUIT
1.13 DIA. FOR .75 CONDUIT

KVA	CATALOG NUMBER		VOLTAGE		NEMA Rating	WEIGHT	PHASE	FREQ.
			HIGH	LOW				
6.0	T-2A-79517-1S		600Δ	480Y/277	3R	140 Lbs	3φ	60 Hz
	A	B	C	D	E	F	G	H
	14.17	12.55	8.47	9.98	11.67	11.83	11.55	8.82

Insulation:	180°C	Encapsulated	Temp Rise:	115°C
-------------	-------	--------------	------------	-------



Type No.

DATE: Jan 9, 2012