



**REVISIONS**

**NOTES:**

- 1. Dry Type
- 2. Class AA
- 3. Ventilated
- 4. Paint - #61 ANSI



Primary Volts	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
504	H1, H2, H3	1	
480	H1, H2, H3	2	
456	H1, H2, H3	3	
Secondary Volts			
208			X1, X2, X3
120 1 phase			X1 to X0 X2 to X0 X3 to X0

KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

KVA	CATALOG NUMBER	VOLTAGE		LUG KIT	WEIGHT	PHASE	FREQUENCY
		HIGH	LOW				
1000	T3001M0012BS	480Δ	208Y/120		5375 Lbs	3φ	60Hz
Temp Rise:	150°C	<b>TYPICAL PERFORMANCE DATA</b>				Typical Efficiency @ 35%	99.35%
Insulation:	220°C	Regulation @ 100% PF	1.00%	Windings:	AL	Typical No Load Losses:	1301.44W
NEMA ST20 Standard:		Standards:	UL/CSA	Impedance:	5.74%	100% Load (Typ) Load Losses (I <sup>2</sup> R)	10,695.18W
Electrostatic Shield:	Option	Approvals:	DOE-2016	Enclosure:	3R	Total Load Losses:	11,996.62W

DATE: 14-Aug-13

TYPE NO:

**CASE 6**

**Meets US DOE 2016 Efficiency**