



# Revisions



Primary Volts	%	Connect Leads to Tap No.
483	105	1
472	102.5	2
460	100	3
449	97.5	4
437	95	5
Secondary Volts		
460		X1, X2, X3
266		X1 & X0 X2 & X0 X3 & X0
1 phase		

KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
550	<b>DTGB-0550-4S</b>	460Δ	460Y/266	WS-A-7	2580Lbs	3φ	60 Hz

Winding Rise:	150°C
Insulation:	220°C
Sound Level:	65db

### TYPICAL PERFORMANCE DATA

Regulation @ 100% PF:	2.39%
Standards:	UL/CSA

Windings:	AL
Impedance:	7.38%

Typical Effic. @ 35%	98.68%
No Load Losses:	1,499 W
Full Load Losses:	13,314 W

Type No. \_\_\_\_\_

DRAWN: \_\_\_\_\_

DATE: October 9, 2014

## CASE 7

		Control 7	A
--	--	--------------	---