



PRIMARY LINES TO H1-H2-H3
SECONDARY LINES TO X0-X1-X2-X3

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

REVISIONS

NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



KVA	CATALOG NUMBER	VOLTAGE		K-FACTOR	WEIGHT	PHASE	FREQUENCY	
		HIGH	LOW					
15	T3015K0013BK4S	480Δ	208Y/120	4	325 Lbs	3	60Hz	
Temp Rise:		150°C	TYPICAL PERFORMANCE DATA				Typical Efficiency @ 35%	
Insulation:		220°C					Regulation @ 100% PF	
NEMA ST20 Standard:		45 dB	Standards:		UL/CSA	Impedance:	100% Load (Typ) Load Losses (I²R)	
Electrostatic Shield:		YES	Approvals:		DOE-2016	Enclosure:	3R	Total Load Losses:

DATE: 25-Jan-16

TYPE NO:

CASE 1

Meets US DOE 2016 Efficiency