



Revisions



KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.



| Primary Volts | % | Connect Leads to Tap No. |
|---------------|-------|--------------------------|
| 604 | 105 | 1 |
| 589 | 102.5 | 2 |
| 575 | 100 | 3 |
| 561 | 97.5 | 4 |
| 546 | 95 | 5 |

| Secondary Volts | | |
|-----------------|--|------------|
| 460 | | X1, X2, X3 |
| 266 | | X1 & X0 |
| 1 phase | | X2 & X0 |
| | | X3 & X0 |

| KVA | CATALOG NUMBER | VOLTAGE | | WEATHER SHIELD | WEIGHT | PHASE | FREQ. |
|-----|---------------------|---------|----------|----------------|---------|-------|-------|
| | | HIGH | LOW | | | | |
| 118 | DTHB-0118-4S | 575Δ | 460Y/266 | WS-A-3 | 714 Lbs | 3φ | 60 Hz |

TYPICAL PERFORMANCE DATA

| | |
|--------------|-------|
| Winding Rise | 150°C |
| Insulation | 220°C |
| Sound Level | 50 dB |

| | |
|------------|--------|
| Impedance: | 6.61% |
| Standards: | UL/CSA |

| | |
|-----------|----|
| Windings: | AL |
|-----------|----|

| | |
|--------------------|--|
| Typical Efficiency | |
| No Load Losses | |
| Full Load Losses | |



Type No.