



Primary Volts	%	Connect Leads to Tap No.
630	105	1
615	102.5	2
600	100	3
585	97.5	4
570	95	5
555	92.5	6
540	90	7
Secondary Volts		
240		X1, X2, X3
120		X1, X4, or X2, X4

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

KEY: DENOTES CONDUIT AREAS

## REVISIONS

### NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



KVA	CATALOG NUMBER	VOLTAGE		LUG KIT	WEIGHT	PHASE	FREQUENCY
		HIGH	LOW				
15	T3015K0323BS	600Δ	240Δ/120		300 Lbs	3φ	60Hz
Temp Rise:	150°C	<b>TYPICAL PERFORMANCE DATA</b>				Typical Efficiency @ 35%	97.98%
Insulation:	220°C	Regulation @ 100% PF	1.80%	Windings:	AL	Typical No Load Losses:	76.05
NEMA ST20 Standard:	45 dB	Standards:	UL/CSA	Impedance:	2.57%	100% Load (Typ) Load Losses (I <sup>2</sup> R)	346.01
Electrostatic Shield:	YES	Approvals:	DOE-2016	Enclosure:	3R	Total Load Losses:	422.06

DATE: 12-Jan-16

TYPE NO:

**CASE 1**

**Meets US DOE 2016 Efficiency**