


PRIMARY VOLTS	%	CONNECT LEADS TO TAP NO.
504	105	1
492	102.5	2
480	100	3
468	97.5	4
456	95	5
444	92.5	6
432	90	7



PRIMARY LINES TO H1-H2-H3
SECONDARY LINES TO X0-X1-X2-X3

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

KEY: DENOTES CONDUIT AREAS

REVISIONS

NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



KVA	CATALOG NUMBER	VOLTAGE		K-FACTOR	WEIGHT	PHASE	FREQUENCY
		HIGH	LOW				
75	T3075K0013BK13S	480Δ	208Y/120	13	938 Lbs	3φ	60Hz
Temp Rise:	150°C	TYPICAL PERFORMANCE DATA				Typical Efficiency @ 35%	98.67%
Insulation:	220°C	Regulation @ 100% PF	1.10%	Windings:	AL	Typical No Load Losses:	258.75W
NEMA ST20 Standard:	50 dB	Standards:	UL/CSA	Impedance:	2.84%	100% Load (Typ) Load Losses (I²R)	1660.78W
Electrostatic Shield:	YES	Approvals:	DOE-2016	Enclosure:	3R	Total Load Losses:	1,919.53W

DATE: 25-Jan-16

TYPE NO:

CASE 3

Meets US DOE 2016 Efficiency