



INPUT CONNECTIONS		
VOLTS	INPUT LINES 1 2	
277	H1	H2
480	H1	H3

OUTPUT CONNECTIONS		
VOLTS	OUTPUT LINES 1 2	
208	X1	X2
277	X1	X3



Type No.

KVA	CATALOG NUMBER	VOLTAGE		WIRING DIAGRAM	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
10	GP12-10000-S	277 /	208 /		125	1	60 Hz

TYPICAL PERFORMANCE DATA			
Winding Rise	115°C	Regulation @ 100% PF	1.8%
Insulation	180°C	IMPEDANCE	2.12
Sound Level	45 dB	Typical Efficiency	97.54%
		Full Load Losses	252 W
		No Load Losses	70.4

A	B	C	D	E	F	G	H	J	K	L	M	N	P	R
14.12	15.93	14.56	11.59	4.54	11.75	16.94	11.62	11.38	2.68	2.44	3.00	3.13	2.00	3.00

					A	PRINTS TO	CONTROL 7	GP12-10000-S
--	--	--	--	--	----------	-----------	------------------	---------------------