





KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.



Primary Volts	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
630	H1, H2, H3	1	
615	H1, H2, H3	2	
600	H1, H2, H3	3	
585	H1, H2, H3	4	
570	H1, H2, H3	5	
555	H1, H2, H3	6	
540	H1, H2, H3	7	

Secondary Volts			
208			X1, X2, X3
120 1 phase			X1 to X0 X2 to X0 X3 to X0

REVISIONS

NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



KVA	CATALOG NUMBER	VOLTAGE		LUG KIT	WEIGHT	PHASE	FREQUENCY				
	T3075K0083BS	HIGH	LOW								
75			600Δ	208Y/120		600 Lbs	3ϕ	60Hz			
Temp Rise:		150°C	TYPICAL PERFORMANCE DATA				Typical Efficiency @ 35%	98.65%			
Insulation:		220°C	Regulation @ 100% PF	2.90%		Windings:	AL	Typical No Load Losses:	153.33		
NEMA ST20 Standard:		50 dB				Standards:	UL/CSA	Impedance:	5.59%	100% Load (Typ) Load Losses (I²R)	2242.45
Electrostatic Shield:		YES					DOE-2016	Enclosure:	3R	Total Load Lossess:	2395.78

Meets US DOE 2016 Efficiency

DATE: 12-Jan-16

TYPE NO:

CASE 2