



BOTTOM

Primary Volts	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
480	H1, H2, H3	1	
456	H1, H2, H3	2	
432	H1, H2, H3	3	

Secondary Volts			
208			X1, X2, X3
120 1 phase			X1 to X0 X2 to X0 X3 to X0

NOTES:

- 1. **KNOCKOUTS:**
1.69 DIA. FOR 1.25 CONDUIT
1.13 DIA. FOR .75 CONDUIT

KVA	CATALOG NUMBER		VOLTAGE		WIRING DIAGRAM	WEIGHT	PHASE	FREQ.
			HIGH	LOW				
6.0	T-2A-53309-SS		480Δ	208Y/12		140	3φ	60 Hz
	A	B	C	D	E	F	G	H
	14.17	12.55	8.47	9.98	11.67	11.8	11.55	8.82
	Insulation	180°C	316 Stainless Steel		Temp Rise:	115°C		



Type No.

DATE: Jan 29,